

6-Outlet Commercial-Grade Surge Protector, 6 ft. (1.83 m) Cord, 900 Joules, 12.5-in. length

MODEL NUMBER: PM6SN1



Highlights

- 6 outlets/6-ft. (1.83 m) cord
- 900 joule rating

Package Includes

- PM6SN1 Power Strip
- Warranty information
- Instruction manual

Description

The PM6SN1 Power Strip offers a convenient method of power distribution and surge suppression in workbench, wall-mount or floor-mount applications. Includes six NEMA 5-15R outlets, six-foot (1.8-meter) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built-in surge suppression rated at 900 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige housing with black output receptacles and power cord.

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1449 3rd Edition (USA/400V rating), UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity
- 6-ft. (1.83 m) AC line cord
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW	
UPC Code	037332101013
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Powering Business Worldwide

TRIPP LITE
SERIES

Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	45000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and lighted two position power switch controls power to all outlets
Diagnostic LED Details	Protection present (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	900
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Up to 20 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Beige
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	165 mm
Outlets Measurement (Center to Center)	38.89mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.25 x 15.00 x 6.00
Shipping Dimensions (hwd / cm)	5.72 x 38.10 x 15.24
Shipping Weight (lbs.)	1.77
Shipping Weight (kg)	0.80
Unit Dimensions (hwd / in.)	1.500 x 12.750 x 2.500
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Unit Weight (lbs.)	1.25
Unit Weight (kg)	0.57
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.