

Replacement Battery Cartridge for Select 48V SmartOnline UPS Systems

MODEL NUMBER: **RBC48S**



Extends the battery life of select 48V Tripp Lite SmartOnline® UPS systems.

Description

The RBC48S Replacement Battery Cartridge breathes new life into select 48V UPS systems whose internal batteries are dead, aging or expired. Built to function in a wide range of operating temperatures, the RBC48S has been carefully screened and certified to restore your UPS system's runtime performance to its original specifications. The leakproof, no-maintenance RBC48S comes preassembled and prewired for quick and easy installation in your UPS system. Reusable packaging holds expired batteries for delivery to the nearest recycling center. Compatible with SUINT2200LCD2U and other models recommending its use.

Features

Replacement Internal Battery for Select 48V UPS Systems

- Screened and certified to restore UPS system's runtime performance to original specs
- compatible with SUINT2200LCD2U and other models recommending its use
- Preassembled and prewired for immediate installation
- Designed for a wide range of operating temperatures
- Rugged leakproof construction
- No maintenance required
- Reusable packaging for delivering expired batteries to recycling center

Specifications

OVERVIEW	
UPC Code	037332192448
BATTERY	
DC System Voltage (VDC)	48
Included Battery Set	Contains (4) 12V 9AH sealed lead acid batteries

Highlights

- Replacement internal battery for select 48V UPS systems
- Rugged leakproof construction
- No maintenance required
- Wide range of operating temperatures
- Preassembled and prewired for immediate installation

Package Includes

- RBC48S Replacement 48V Battery Cartridge



Powering Business Worldwide

TRIPP LITE
SERIES

Typical Battery Lifespan	3 to 5 years, depending on UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.70 x 11.70 x 14.60
Shipping Dimensions (hwd / cm)	14.48 x 29.72 x 37.08
Shipping Weight (lbs.)	27.10
Shipping Weight (kg)	12.29
Unit Dimensions (hwd / in.)	2.640 x 8.300 x 12.040
Unit Dimensions (hwd / cm)	6.71 x 23.0 x 34.0
Unit Weight (lbs.)	26
Unit Weight (kg)	11.79
ENVIRONMENTAL	
Relative Humidity	Up to 95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
Storage Elevation (ft.)	10,000 ft.
Storage Elevation (m)	3000m
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.