

## UPS Replacement Battery Cartridge for APC, Belkin, Best, Powerware, Liebert & Other UPS

MODEL NUMBER: RBC51



### Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

### Package Includes

- RBC51 UPS Replacement Battery Cartridge
- Owner's Manual

### Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original manufacturer specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with a wide variety UPS brands and models. See the UPS replacement battery web page to confirm compatibility and quantity required.

### Features

- Restores UPS runtime performance to its original runtime specifications
- Reusable packaging contains expired batteries for recycling center delivery
- Compatible with a variety of UPS brands

## Specifications

OVERVIEW	
UPC Code	037332118660
Brand Compatibility	Compatible with a variety of UPS Brands
BATTERY	
Included Battery Set	Contains (1) 12V 9AH sealed lead acid battery with F2 (6.35 mm / 0.25 inch) connection terminals
Typical Battery Lifespan	3 - 5 years, depending on host UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.90 x 11.90 x 7.40
Shipping Dimensions (hwd / cm)	14.99 x 30.23 x 18.80



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Weight (lbs.)	8.00
Shipping Weight (kg)	3.63
Unit Dimensions (hwd / in.)	1.900 x 4.000 x 5.500
Unit Dimensions (hwd / cm)	9.4 x 6.4 x 14.9
Unit Weight (lbs.)	5.8
Unit Weight (kg)	2.63
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
Storage Elevation (ft.)	0 - 50,000
Storage Elevation (m)	0 - 15,200 m
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.