

1U Rack-Mount Power Strip, 120V, 20A, L5-20P, 12 Outlets (6 Front-Facing, 6-Rear-Facing) 15 ft. (4.57 m) Cord

MODEL NUMBER: **RS-1215-20T**



Highlights

- Designed for standard 19-in. racks (1U high)
- 12 NEMA5-15/20R outlets (6 front/6 rear)
- 15-ft. (4.57 m) cord with locking NEMA L5-20P input plug
- 20A circuit breaker

Description

The RS-1215-20T Power Strip offers 20A capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rack-mount, wall-mount and under-counter installation. Uses only 1U when installed in any 19-inch rack meeting EIA standards. Unfiltered electrical pass-through makes RS-1215-20T ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 12 NEMA5-15/20R outlets (six front/six rear), 15-foot (4.6-meter) cord with locking NEMA L5-20P input plug and lighted switch with cover that prevents risk of accidental turn-off.

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19-in. rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 x NEMA5-15/20R output receptacles (6 front/6 rear)
- 15-ft. (4.57 m) AC cord with NEMA L5-20P input plug
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn-off
- 20A electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
UPC Code	037332119704



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V dedicated line
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA L5-20P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Receptacles	(12) 5-15/20R
Circuit Breaker (amps)	20
Overload Protection	20A circuit breaker
Transformer Accommodation	(5) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted power switch
Locking Switch Cover	Yes
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Form Factors Supported	1U rackmount, wallmount
Housing Color	Black
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	Distance between Front outlets = 2.03 in.; Distance between Rear outlets = 2.79 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	9.30 x 2.60 x 20.20
Shipping Dimensions (hwd / cm)	23.62 x 6.60 x 51.31
Shipping Weight (lbs.)	5.90
Shipping Weight (kg)	2.68



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Dimensions (hwd / in.)	2.000 x 9.000 x 4.500
Unit Dimensions (hwd / cm)	4.3 x 44.4 x 11.4
Unit Weight (lbs.)	5.4
Unit Weight (kg)	2.45
Mounting Details	Includes Rackmount flanges
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.