

SmartRack Pass-Through Side Panel with Key-Locking Latches for 42U Server Rack Cabinet, 2 Panels

MODEL NUMBER: SR42SIDEPT



Locking pass-through steel panels attach to the sides of your SR42UB-based server rack enclosure.

Features

Steel Pass-Through Side Panels for Installation on Your 42U Rack Cabinet

The SmartRack® SR42SIDEPT side panels feature pre-installed key-locking latches for securing your rack equipment against tampering and theft. Designed for standard-depth SR42UB rack frame, this panel can also be added to the side of an expansion cabinet (SR42UBEXP) when application needs have changed or onto a wide cabinet (SR42UBWD) as the depth remains the same. They can also be used as replacements for existing side panels.

Convert an Expansion Cabinet into a Cabinet with Side Panels

When needs change and you want to separate your expansion rack cabinets (such as SR42UBEXP), add four** SR42SIDEPT heavy-duty steel panels to the sides of them to convert the racks into standard cabinets with additional cable management functionality. **Note:** This package includes two (2) singular panels. You will need to purchase four SR42SIDEPT panels total to completely populate an expandable rack.

Highlights

- Pre-installed latches lock securely with included keys to protect equipment from theft
- Brushed slots reduce dust ingress and allow easy cable routing in and out of the rack
- Made from heavy-duty steel engineered to stand up to busy IT environments
- Designed for use with 42 in. (1050 mm) depth, 42U rack enclosures
- Fits models based on the SR42UB frame design, including SR42UBEXP and SR42UBWD

Package Includes

- (2) Side panels with locking latches
- (2) Keys

Specifications

OVERVIEW	
UPC Code	037332179128
Accessory Type	Side Panel
Accessory Class	Rack Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	36.00 x 4.00 x 41.50
Shipping Dimensions (hwd / cm)	91.44 x 10.16 x 105.41
Shipping Weight (lbs.)	43.00



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (kg)	19.50
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	96.52 x 82.55 x 1.91
Unit Weight (lbs.)	19.5
Unit Weight (kg)	8.85
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.