


Toolless Horizontal 90-Degree Elbow for Fiber Routing System, 240 mm (10 in.)

MODEL NUMBER: SRFC10ELBOW



240 mm elbow section turns a straight horizontal run in your fiber management system into a 90-degree turn.

Features

High-Impact PVC Elbow Helps You Create 90-Degree Fiber Cable Routing Schemes

The SmartRack® SRFC10ELBOW connects to two channel sections or other fittings in your fiber routing system to create a 90-degree turn. Two of SRFC10CPL10 couplers (sold separately) are required to complete your installation. Made from durable, lightweight PVC material, this elbow connects using the couplers' included hardware to help keep your fiber optic cable bundles neat and organized. Screws tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space.

Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed
- Requires 2 SRFC10CPL10 couplers (sold separately)

Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

System Requirements

- 2 x SRFC10CPL10 couplers (sold separately)

Package Includes

- Horizontal 90° elbow, 240 mm
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332240835
Product Type	Elbow
Accessory Type	Cable Management Accessories
Cable Management System Component Type	Elbow
PHYSICAL	
Color	Yellow
Shipping Dimensions (hwd / in.)	15.35 x 15.35 x 5.11
Shipping Weight (kg)	1.33
Unit Dimensions (hwd / in.)	4.646 x 14.880 x 14.880
Unit Dimensions (hwd / cm)	11.785 x 37.795 x 37.795



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (lbs.)	1.20
Unit Weight (kg)	0.54
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.