


SmartRack Cable Entry Gland Plate for NEMA-Rated Enclosure Cabinets, 21-Port Membrane

MODEL NUMBER: **SRGP3RM**



Cable entry plate covers entry/exit cable cutouts on SmartRack NEMA 3R and NEMA 4 industrial enclosures.

Features

Gasketed Cable Entry Plate for NEMA-Rated Industrial Enclosures

This metal-reinforced gland plate covers cable entry and exit cutouts on SmartRack® NEMA 3R and NEMA 4 industrial enclosures, including the SRN and SRIN series. The SRGP3RM is sized to correspond to the enclosures' cable cutouts, making it quick and easy to install. Twenty-one ports accept a wide range of cable sizes, including 3 mm to 7 mm (14), 4 mm to 12 mm (six) and 16 mm to 27 mm (one). Membrane seals around non-terminated cables maintain the enclosure's NEMA 3R or NEMA 4 rating. Unused ports also are protected against dust and moisture.

Highlights

- Rugged gasketed cable gland plate with metal reinforcement for long life
- Ideal for high-density cable installations and indoor or outdoor use
- Features 21 ports in various cable sizes ranging from 3 mm to 27 mm
- Membrane seals maintain NEMA rating of SmartRack industrial enclosure
- Unused ports are protected against dust and moisture

System Requirements

SmartRack NEMA 3R and NEMA 4 industrial enclosures

Package Includes

- SRGP3RM Cable Entry Plate
- (6) M5 screws
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332262905
Accessory Type	Gland Plate
Accessory Class	Rack Accessories
PHYSICAL	
Total Number of Ports	21
Shipping Dimensions (hwd / in.)	2.87 x 8.37 x 15.75
Shipping Dimensions (hwd / cm)	7.30 x 21.27 x 40.00
Shipping Weight (lbs.)	2.43
Shipping Weight (kg)	1.11
Unit Dimensions (hwd / in.)	1.260 x 13.386 x 5.906



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (lbs.)	2.00
Unit Weight (kg)	0.91
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
Outdoor Use	Yes
STANDARDS & COMPLIANCE	
Product Compliance	REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.