

Cable Retaining Post for 1.5 in. Wide Cable Runway, Straight and 90-Degree - Hardware Included

MODEL NUMBER: SRLPOST



Increases the volume of cabling running through your cable ladder system and prevents it from spilling over the sides of the runway.

Features

Convenient Cable Retaining Post Secures and Organizes Cables on Your Ladder System This exclusive SmartRack cable retaining post kit creates a secure retaining point between sections of cable ladder to increase the cable runway system's volume. It helps you route stubborn cables, allowing for sharper turns and preventing cabling from flowing over the edge of the ladder. All mounting and installation hardware is included. The cable retaining kit fits solid and tubular steel runway measuring 1.5 x 0.375 inches (38 x 9.5 millimeters). The SRLPOST is designed for SRCABLELADDER, SRCABLELADDER18, SRL90BEND12, SRL90BEND18 and other compatible straight and 90-degree ladder sections.

Highlights

- Provides extra cable depth to existing 1.5 in. (38 mm) wide cable runway installations
- Compatible with 12 in. and 18 in. straight and 90-degree-bend ladder sections
- Fits solid and tubular steel runway measuring 1.5 x 0.375 in. (38 x 9.5 mm)
- Works with all SmartRack® ladder system accessories and runways
- Includes all necessary mounting and installation hardware for immediate use

Applications

- Increase total cable volume without worrying about it spilling over the sides of the ladder
- Keep stubborn cables affixed to the post without needing to tie to other cables

System Requirements

- Compatible with straight and 90-degree-bend ladder sections, including SRCABLELADDER, SRCABLELADDER18, SRL90BEND12 and SRL90BEND18

Package Includes

- (2) Cable runway posts
- (2) Post brackets
- (2) M6 x 35 bolts
- (2) M6 lock washers
- (2) M6 hex nuts
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332214553
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Cable Jacket Color	Black



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	3.10 x 3.30 x 10.20
Shipping Dimensions (hwd / cm)	7.87 x 8.38 x 25.91
Shipping Weight (lbs.)	0.68
Shipping Weight (kg)	0.31
Unit Dimensions (hwd / in.)	3.100 x 3.300 x 10.200
Unit Dimensions (hwd / cm)	7.87 x 8.38 x 25.91
Unit Weight (lbs.)	0.672
Unit Weight (kg)	0.30
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.