

FC to LC 50/125 OM3 10 Gb Adapter for Multi-Function Optical Fiber Cable Tester (M/F)

MODEL NUMBER: **T020-001-LC10G**



Converts FC connector on Tripp Lite Multi-Function Optical Fiber Cable Tester to an LC connector. Ideal for cable installers or anyone else working in telecom or LAN environments.

Description

The T020-001-LC10G FC to LC 10 Gb Adapter converts a native FC fiber female port on the T020-001-PSF Multi-Function Optical Fiber Cable Tester to an LC female port for 50/125 OM3 multimode cable testing. "OM3" is clearly labeled on the unit to differentiate the T020-001-LC10G from other adapters. Included dust caps keep the connectors clean when not in use.

Features

Converts Cable Tester's FC Connector to an LC Connector

- Ideal for cable installers or anyone else working in telecom or LAN environments
- Perfect for 50/125 OM3 multimode cable testing
- FC male plug connects to cable tester's FC female jack
- Included dust caps keep connectors clean
- For use with T020-001-PSF Multi-Function Optical Fiber Cable Tester

Specifications

OVERVIEW	
UPC Code	037332197665
Technology	Multimode
Optical Mode	OM3
PHYSICAL	
Color	Beige; Silver
Clad Diameter (microns)	125

Highlights

- Converts native FC jack to an LC female connector
- FC male plug connects to fiber cable tester's FC female jack
- Perfect for 50/125 OM3 multimode cable testing
- Included dust caps keep connectors clean
- For use with T020-001-PSF Optical Fiber Cable Tester

System Requirements

- T020-001-PSF Multi-Function Optical Fiber Cable Tester

Package Includes

- T020-001-LC10G FC to LC 50/125 OM3 10 Gb Adapter



Powering Business Worldwide

TRIPP LITE
SERIES

Core Diameter (microns)	50
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.