

Conference Power Surge Protector - 4 NEMA 5-15R Outlets, 4 USB-A Ports, 6-ft. (1.83 m) Cord, Black

MODEL NUMBER: **TLP406USBUFO**



Safely charges and powers up to 8 mobile devices, including laptops, during important workplace meetings and conferences.

Features

Keep Your Team's Devices Powered and Charged During Important Meetings

Workplace meetings involve a variety of devices – laptops, smartphones, tablets – to keep everyone coordinated and up to date with the information necessary to make important decisions. Guaranteeing those devices remain charged and powered is Conference Power Surge Protector. Rounded to ensure equal access to everyone at the table, this UL-certified surge protector delivers ample power and reliable protection to as many as eight mobile devices at the same time.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your laptops, projector, printer or other conference-table electronics into four NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. Each outlet is located far enough apart from the others to accept bulky transformers without blocking adjacent outlets.

4 USB-A Ports Share 4.2 Amps of Charging Power

The USB ports are available for charging your smartphones, tablets and other USB mobile devices. They share 4.2A of charging power, which is plenty for delivering ample power to demanding devices.

1800 Joules Safeguard Your Sensitive Electronics

This Protect It!® surge protector features a surge suppression rating of 1800 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP406USBUFO protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Premium Safety Features Protect Your Valuable Equipment

The on/off switch provides one-touch control over all connected equipment. Red and green LEDs confirm your connected equipment is grounded and protected.

Highlights

- Ideal for conference tables, meeting rooms and other areas with multiple mobile devices
- 4 NEMA 5-15R outlets spaced widely apart to accommodate bulky transformers
- 1800 joules protect your valuable electronics against dangerous surges and spikes
- 4 USB ports share 4.2A for fast charging of phones, tablets and other mobile devices
- Right-angle NEMA 5-15P plug with 6-ft. (1.83 m) cord allows easy connection in confined spaces

Applications

- Keep vital mobile devices fully powered and charged during important conferences and meetings
- Protect laptops, tablets, smartphones and other valuable electronics against AC power surges and spikes
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges

Package Includes

- TLP406USBUFO Conference Power Surge Protector
- Owner's manual

Right-Angle Plug Makes Connecting in Tight Spaces Easier

The space-saving right-angle NEMA 5-15P connector with 6-ft. (1.83 m) braided power cord is easy to install in confined spaces, such as behind a computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Specifications

OVERVIEW	
UPC Code	037332260734
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	1800
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT-B
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	4
Total Charging Watts	21



Powering Business Worldwide

TRIPP LITE
SERIES

Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(4) 4.2A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1800
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	800,800,800
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black; Gray
Mounting Holes or Slots	Yes
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	3.10 x 7.30 x 7.30
Shipping Dimensions (hwd / cm)	7.87 x 18.54 x 18.54
Shipping Weight (lbs.)	1.70
Shipping Weight (kg)	0.77
Unit Dimensions (hwd / in.)	2.000 x 7.080 x 7.080
Unit Dimensions (hwd / cm)	5.08 x 18 x 18
Unit Weight (lbs.)	1.4
Unit Weight (kg)	0.64
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH



Powering Business Worldwide

TRIPP LITE
SERIES

Storage Humidity Range	0% to 90% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); NOM (Mexico); UL 1449; UL 497A; UL 1363
Product Compliance	FCC Part 68; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$2,500 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.