

## 7-Outlet Surge Protector - 6 on strip/1 in detachable plug, 2 USB Ports (2.4A Shared), Detachable Charger Plug, 6 ft. Cord, 5-15P Plug, 900 Joules, White

MODEL NUMBER: **TLP616USB**



Surge protector with detachable charger plug protects your electronic devices against dangerous surges, spikes and line noise.

### Features

#### 7-Outlet Surge Protector with USB Charging Safeguards Your Sensitive Electronics

Ideal for your home or office workstation or home theater, this Protect It!® seven-outlet surge protector features a surge suppression rating of 900 joules to defend your sensitive electronic components against even the strongest power surges and spikes.

#### Detachable Plug Provides Power and Charging at Home and on the Go

The six-foot braided cord and space-saving right-angle NEMA 5-15P plug allows you flexibility in placing the unit behind furniture or other tight places. Keyhole mounts on the rear allow for wall installation. For travel use, remove the plug to take a separate USB wall charger with you in your purse, briefcase or laptop bag. The detachable USB charger plug features one NEMA 5-15R outlet (without surge protection) and both USB ports.

#### NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your PC, printer, wireless router, game console, television, sound system or other home/office devices into the strip's six NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise.

#### 2 USB Ports Share 2.4 Amps of Charging Power

Two USB-A ports are available for charging your smartphone, tablet or other USB mobile devices. They share 2.4A for charging multiple devices at the same time.

#### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

#### Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

The lighted on/off switch allows you easy one-touch control over equipment connected to the strip. An

### Highlights

- Detachable plug provides a separate USB charger with included AC outlet
- 7 total NEMA 5-15R outlets - 6 on strip/1 on detachable plug - for powering computers, printers and other electronic devices
- 900 joules protect your valuable electronics against dangerous surges and spikes
- 2 USB ports share 2.4A for fast charging of phones, tablets and other mobile devices
- Right-angle NEMA 5-15P plug with braided 6 ft. cord allows connection in tight spaces

### Applications

- Protect a computer, router and other valuable electronics against AC power surges and spikes
- Detach the plug to carry a separate USB charger with AC outlet in your laptop bag, share power and charging in meeting or at home
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges
- Charge a smartphone and tablet without taking up available AC outlets

### Package Includes

- TLP616USB 7-Outlet Surge Protector, White
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

integrated 15-amp resettable circuit breaker helps prevent overloads. A green LED confirms your connected equipment is protected.

## Specifications

OVERVIEW	
UPC Code	037332260314
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Amazon Kindle; Headphones; Laptop; Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Cord Gauge Type	16 gauge
Input Cord Gauge (AWG)	16
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(2) 5-15/20R
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6 outlets; 1 outlet in wall plug
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
CHARGING	
Number of Charging Ports	2
Total Charging Watts	12



Powering Business Worldwide

TRIPP LITE  
SERIES

Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 2.4A
Overcharge Protection	No
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	900
AC Suppression Response Time	< 1 ns
UL1449 Let Through Rating	L-N 700
EMI / RFI Filtering	Yes
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	White and Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Receptacle Color	Black
Shipping Weight (lbs.)	1.40
Shipping Weight (kg)	0.64
Unit Dimensions (hwd / in.)	10.400 x 2.100 x 1.300
Unit Dimensions (hwd / cm)	26.4 x 5.3 x 3.3
Unit Weight (lbs.)	1.23
Unit Weight (kg)	0.56
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH
Storage Humidity Range	0% to 90% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No



Powering Business Worldwide

TRIPP LITE  
SERIES

Antimicrobial	No
GaN Technology	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 497A; UL 1363; UL Listed
Product Compliance	FCC Part 68; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.