

Protect It! 2-Outlet Travel-Size Surge Protector - 5-15R Outlets, USB-C and USB-A Ports, 5-15P Input, Black

MODEL NUMBER: TRAVELER3USBC



Protects your laptop and other electronics against dangerous power surges, spikes and line noise in a hotel or conference room.

Features

2-Outlet Surge Protector with USB Charging Safeguards Your Sensitive Electronics

Ideal for use in a hotel, airport, conference room or anywhere else you use your laptop, this Protect It!® surge protector features a surge protection rating of 306 joules to defend your valuable electronic components against power surges and spikes. The 18-inch (45.7-centimeter) AC power cord with right-angle NEMA 5-15P plug connects to a wall outlet and conveniently wraps around the unit for easy storage when not in use.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your laptop, printer, external hard drives and other portable electronics into two NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. One outlet is in front of the surge protector and the other is on the back side to help accommodate a bulky transformer without blocking the other outlet.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

USB Charger Keeps Mobile Devices Ready for Use

One USB-C port and one USB-A port are available for charging your smartphone, tablet, MP3 player or other USB mobile devices. The USB-C port has 3A and the USB-A port 2.4A for charging multiple devices at the same time. A green LED confirms at a glance that your equipment is protected.

Specifications

Highlights

- 2 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment
- 306 joules protect your valuable electronics against dangerous surges and spikes
- Portable housing with concealable 18 in. power cord easy to carry in laptop bag
- USB-A and USB-C ports power and charge smartphones and other mobile devices
- Easy-to-see green LED lets you know at a glance that your equipment is protected

Package Includes

- TRAVELER3USBC 2-Outlet Travel-Size Surge Protector, Black
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT 3/C
Input Cord Length (ft.)	1.5
Right-Angle Plug	Yes
Input Cord Length (m)	0.46
Integrated Cord Clip	No
OUTPUT	
Output Capacity (Watts)	1560
Frequency Compatibility	60 Hz
Output (Watts)	1560
Output Receptacles	(2) 5-15R
Transformer Accommodation	(2) Yes
Output Amp Capacity	13
Right-Angle Outlets	No
CONNECTIONS	
Number of Ports	2
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LED confirmr suppressor "protection present" (green) status
CHARGING	
Number of Charging Ports	2
Total Charging Amps	1 USB-A 5V/2.4A, 1 USB-C 5V/3A
Charging Method	USB
Charging Port Type	(1) USB A (FEMALE); (1) USB C (FEMALE)
Charging Ports / Amps	(1) 2.4A; (1) 3A



Powering Business Worldwide

TRIPP LITE
SERIES

Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	306
Protection Modes	L-N
UL1449 Let Through Rating	1200
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Gray
Housing Color	Black; Gray
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.88 x 1.68 x 6.20
Shipping Dimensions (hwd / cm)	7.32 x 4.27 x 15.75
Shipping Weight (lbs.)	0.57
Shipping Weight (kg)	0.26
Unit Dimensions (hwd / in.)	2.280 x 1.240 x 5.840
Unit Dimensions (hwd / cm)	5.79 x 3.15 x 14.83
Unit Weight (lbs.)	0.49
Unit Weight (kg)	0.22
Input Cord Color	Gray
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No



Powering Business Worldwide

TRIPP LITE
SERIES

GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); UL 1449; UL Listed; cUL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.