

## USB-A to RJ45 Rollover Console Cable (M/M) - Cisco Compatible, 250 Kbps, 6 ft. (1.83 m), Black

MODEL NUMBER: U009-006-RJ45-X



Rollover console cable connects your computer or laptop's USB-A port to a serial-based Cisco device with a console port.

### Features

**Ideal for IT Pros Who Need a Connection Between Computer and Cisco Console Device** This rollover cable is designed for consumers or IT professionals who want a reliable connection between their computer or laptop's USB-A port and a Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port. The cable works with both older and new Cisco models, supporting data transfer rates up to 250 Kbps.

**Top-Quality Construction for Top-of-the-Line Performance** No extra software or external power is required to use this 6-ft. (1.83 m) cable. Premium double shielding eliminates crosstalk and reduce EMI/RFI line noise that can disturb your electronics and inflict hardware damage or data loss. The U009-006-RJ45-X is compatible with Windows (up to 11), Mac (up to 10.12) and Linux (up to Redhat 9.0) operating systems.

## Specifications

OVERVIEW	
UPC Code	037332222107
Technology	Cat5/5e; USB
Host Connector	USB A (MALE)
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Side A - Connector 1	USB A (MALE)

### Highlights

- Great for programming, resetting or rebooting a Cisco switch, firewall, router or modem
- 6-ft. (1.83 m) cable supports data transfer speeds up to 250 Kbps
- Double-shielded construction cuts crosstalk and EMI/RFI line noise
- Plug-and-play operation with no software required for easy, immediate installation
- Compatible with Windows, Mac and Linux

### Applications

- Program, reset or reboot a serial-based Cisco switch, firewall, router or modem through its console port

### System Requirements

- Computer or laptop with USB-A port
- Serial-based Cisco device with console port
- Windows (up to 11), Mac (up to 10.12), or Linux (up to Redhat 9.0) operating systems

### Package Includes

- U009-006-RJ45-X USB to RJ45 Rollover Console Cable (M/M), Black, 6-ft. (1.83 m)



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	RJ45 (MALE)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	PVC, PE
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	5.5mm; 4.7mm +/- 0.15
Wire Gauge (AWG)	26
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Cable Length (cm)	183
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.1984
Unit Weight (kg)	0.09
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0-90% non-condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 1.1 (up to 12 Mbps)
IP68 Rated	No
IP20 Rated	No
Driver Required	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty