

## USB-A to USB-C Flat Cable - M/M, USB 2.0, Black, 6 ft. (1.83 m)

MODEL NUMBER: U038-006-FL



Flat USB cable connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

### Features

**Flat USB 2.0 Cable Charges and Syncs Your Phone or Other USB-C Mobile Device** This USB sync/charge cable (M/M) connects your smartphone, tablet, MacBook Pro, Windows laptop or other USB-C device to the USB-A port on a computer, wall charger or car charger. It supports power output up to 3 amps (60 watts), which is sufficient for fast charging and powering most mobile devices. It also simultaneously synchronizes and transfers data at USB 2.0 speeds up to 480 Mbps.

**Innovative Flat Cable Prevents Tangles, Allows Flexible Bends** Very flexible for convenient on-the-go connections, this flat cable avoids nasty tangles in your backpack or laptop bag. Its advanced flat design allows easy rolling for tangle-free storage. Plus, it bends easily for connecting to devices in tight spaces or around obstacles.

**Reversible USB-C Connector Attaches in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

### Highlights

- Flexible flat design helps prevent inconvenient tangling and allows easy bending
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charging and data transfers
- Supports 3A (60W) power output for charging, syncing and powering mobile devices
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB-A to USB-C cable is compatible with all USB-A, USB-C and Thunderbolt 3 devices

### Applications

- Charge and power your MacBook Pro, Windows laptop or other USB-C device from a USB-A computer or wall charger up to 6 ft. away
- Connect a USB printer or hub to a PC's hard-to-reach rear USB-C or Thunderbolt 3 port
- Roll tightly for convenient carrying in your laptop bag, backpack or briefcase as a flexible spare cable

### System Requirements

- Device or charger with USB-A port
- Device with USB-C or Thunderbolt 3 port

### Package Includes

- U038-006-FL USB-A to USB-C Flat Cable (M/M), Black, 6 ft. (1.8 m)

## Specifications

OVERVIEW	
UPC Code	037332253996
Technology	USB 2.0 (High Speed)
Cable Type	Passive
INPUT	
Maximum Input Amps	3



Powering Business Worldwide

TRIPP LITE  
SERIES

Maximum Input Watts	60
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	2.1*6.2 mm
Wire Gauge (AWG)	22/22
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.04
Unit Packaging Type	Polybag
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.