

## USB-C Flat Cable (M/M), USB 2.0, Black, 3 ft. (0.91 m)

MODEL NUMBER: **U040-003-C-FL**



Flat USB cable connects a smartphone or other USB-C device to the USB-C port on your computer, charger or power bank.

### Features

**Flat USB 2.0 Cable Charges and Syncs Your Phone or Other USB-C Mobile Device** This USB sync/charge cable (M/M) connects your smartphone, tablet, MacBook Pro, Windows laptop or other USB-C device to the USB-C port on a computer, docking station or wall charger. It supports power output up to 3 amps (60 watts), which is sufficient for fast charging and powering most mobile devices. It also simultaneously synchronizes and transfers data at USB 2.0 speeds up to 480 Mbps.

**Innovative Flat Cable Prevents Tangles, Allows Flexible Bends** Very flexible for convenient on-the-go connections, this flat cable avoids nasty tangles in your backpack or laptop bag. Its advanced flat design allows easy rolling for tangle-free storage. Plus, it bends easily for connecting to devices in tight spaces or around obstacles.

**Reversible USB-C Connectors Attach in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

### Highlights

- Flexible flat design helps prevent inconvenient tangling and allows easy bending
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charging and data transfers
- Supports 3A (60W) power output for charging, syncing and powering mobile devices
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- Flat USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

### Applications

- Charge and power your MacBook Pro, Windows laptop or other USB-C or Thunderbolt 3 device from a USB-C wall charger up to 3 ft. away
- Transfer data between an external hard drive and your laptop or PC
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port
- Roll tightly for convenient carrying in your laptop bag, backpack or briefcase as a flexible spare cable

### System Requirements

- Devices with USB-C or Thunderbolt 3 ports

### Package Includes

- U040-003-C-FL USB-C to USB-C Cable, M/M, Black, 3 ft. (0.9 m)

## Specifications

OVERVIEW	
UPC Code	037332254009
Technology	USB 2.0 (High Speed)
Cable Type	Passive
INPUT	



Powering Business Worldwide

TRIPP LITE  
SERIES

Maximum Input Amps	3
Maximum Input Watts	60
<b>POWER</b>	
USB Power Delivery (PD) Charging Support	Yes
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	2.1*5.8 MM
Wire Gauge (AWG)	30/24
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Packaging Type	Polybag
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	5% to 90%, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
<b>STANDARDS &amp; COMPLIANCE</b>	



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.