

USB-C Cable (M/M) - USB 2.0, Right-Angle Plug, Black, 2 m (6.6 ft.)

MODEL NUMBER: U040-02M-C-RA



Connects a smartphone, Nintendo Switch 2 or other USB-C device to the USB-C port on your computer, charger or power bank.

Features

USB-C Cable Connects Devices for Charging or Transferring Data

This USB cable (M/M) is compatible with any device with a USB-C or Thunderbolt 3 port, including MacBook Pros, Chromebooks and Windows laptops, as well as the Nintendo Switch 2. It allows you to connect your notebook computer to a docking station, your Apple or Android device to a wall charger or power bank, or an external hard drive to a PC or tablet, to name just a few valuable uses for the cable.

PD Charging Cable Supports up to 60W for Syncing and Charging Mobile Devices

The Power Delivery cable provides power output up to 20V 3A (60W), which is sufficient for fast charging, syncing and powering most smartphones and other mobile devices. It also supports USB 2.0 data transfer rates up to 480 Mbps. The USB-C to USB-C cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Right-Angle Plug Makes Connecting in Tight Spaces Easier

A space-saving right-angle USB-C connector is easy to install in confined spaces, such as behind your computer or workstation. The right-angle construction also helps relieve strain on the cable and connector and prevents the cable from bending awkwardly.

Reversible USB-C Connectors Attach in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

Specifications

OVERVIEW	
UPC Code	037332263681
Technology	USB 2.0 (High Speed)
Cable Type	Passive

Highlights

- Power Delivery cable supports 20V 3A (60W) power output for charging host device
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- Space-saving right-angle USB-C plug allows easy connection in confined spaces
- Compatible with all USB-C and Thunderbolt 3 devices, including Nintendo Switch 2

System Requirements

Devices with USB-C or Thunderbolt 3 ports

Package Includes

U040-02M-C-RA USB-C to USB-C Cable, M/M, Black, 2 m (6.6 ft.)



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Maximum Input Amps	3
Maximum Input Watts	60
POWER	
USB Power Delivery (PD) Charging Support	Yes
CONNECTIONS	
Side A - Connector 1	USB C (MALE) - RIGHT ANGLE
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Angled
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5MM
Cable Length (ft.)	6.6
Cable Length (m)	2.01
Cable Length (in.)	78.7
Shipping Dimensions (hwd / in.)	0.50 x 6.75 x 9.50
Shipping Weight (kg)	0.06
Unit Dimensions (hwd / in.)	0.500 x 6.750 x 9.500
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	10% to 85%, Non-Condensing
Power Provided to Connected Device(s)	60W (20V/3A)
FEATURES & SPECIFICATIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.