

2-Port USB 3.0 SuperSpeed Desktop Extension Cable A (M/2xF), 6 ft. (1.83 m)

MODEL NUMBER: U324-006-DSK2



Converts your computer's USB 3.0 port to 2 USB 3.0 ports and extends them up to 6 ft away. Ideal for connecting thumb drives, digital cameras and other USB-A devices.

Features

Expands an Existing USB 3.0 Port to 2 Ports and Extends Them an Extra 6 ft.

- Move a hard-to-reach USB port within easy access
- Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices
- Features one USB 3.0 data/power port and one power-only port

Enjoy SuperSpeed Transfer Rates in High-End Applications

- Supports data transfer rates up to 5 Gbps—10x the speed of USB 2.0
- Bi-directional interface allows data to flow both directions at the same time, increasing theoretical bandwidth by 10x
- Backward compatible with earlier USB generations

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding blocks EMI/RFI interference
- Molded nickel-plated connectors ensure excellent connectivity
- Integral strain relief for cable and connectors' long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces
- Black padded non-sliding base

Specifications

Highlights

- Supports data transfer rates up to 5 Gbps
- Bi-directional interface allows data to flow both directions
- Backward compatible with previous USB generations
- Features one USB 3.0 data/power port and one power-only port
- Double-shielded protection against EMI/RFI line noise
- Black padded non-sliding base

System Requirements

- Computer, laptop or other device with USB 3.0 port (to achieve USB 3.0 speeds)

Package Includes

- U324-006-DSK2 2-Port USB 3.0 SuperSpeed Desktop Extension Cable (M/2xF), 6 ft.

OVERVIEW

UPC Code

037332199478



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	USB 3.x
Cable Type	Passive
INPUT	
Maximum Input Amps	2
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
CHARGING	
Total Charging Watts	10
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5mm
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	5.31 x 3.94 x 0.50
Shipping Dimensions (hwd / cm)	13.49 x 10.01 x 1.27
Shipping Weight (lbs.)	0.24
Shipping Weight (kg)	0.11
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 131°F (-10° to 55°C)
Relative Humidity	5% to 90% RH, Non-Condensing
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	10W (5V/2A)



Powering Business Worldwide

TRIPP LITE
SERIES

FEATURES & SPECIFICATIONS	
Over Current Protection	Yes
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)
Data Transfer Rate	5 Gbps
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.