

6-Port USB Charging Hub - USB 3.x (5Gbps) and USB 2.0, Dedicated Charging Port

MODEL NUMBER: **U360-412**



Charge an iPad or tablet via a USB hub.

Description

The U360-412 USB 3.0 Charging Hub plugs into a computer's USB 3.0 port and provides two USB 3.0 SuperSpeed peripheral ports, four USB 2.0 High-Speed peripheral ports and one charging port for charging tablets. Two USB 2.0 ports have convenient top plugging for thumb drive access. Dedicated 2A charging port supplies the extra amperage needed to charge tablets. Plug-and-Play, so no software or drivers are required. Automatically switches to the highest speed supported by the peripheral. Windows (compatible with Windows 10) and macOS compatible.

Features

- USB 3.0 ports support 5Gbps transfer speeds when plugged into a USB 3.0 computer and peripheral
- USB 2.0 ports support High-Speed 480Mbps speeds
- Charging port provides 5V,2A for tablet (iPad) full battery charging
- USB 3.0 ports support up to 900mA per port
- USB 2.0 ports support up to 500mA per port
- The included external power supply provides 4A of power, to be shared between the hub ports (up to 2A for iPad charging port, up to 900mA per USB 3.0 port, up to 500mA per USB 2.0 port)
- Top mount ports for Thumb Drive connections
- Plug-and-Play
- No software or drivers required
- Windows (compatible with Windows 10) and Mac compatible
- Overcurrent protection
- LED power indicator light

Specifications

OVERVIEW

UPC Code	037332173560
----------	--------------

Highlights

- USB 3.0 Hub with two USB 3.0 SuperSpeed ports and four USB 2.0 High-Speed ports
- One dedicated port for Tablet charging (5V, 2A)
- USB 3.0 ports support up to 900mA per port
- USB 2.0 ports support up to 500mA per port
- Plug-and-Play - no software or drivers required

System Requirements

- USB 3.0 or 2.0 computer
- USB 3.0 or 2.0 peripherals

Package Includes

- USB 7-port Hub
- USB 3.0 A-B cable, 3ft
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.9A; Output: 5V, 4A)



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Hub
Technology	USB 3.x
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(6) USB A (FEMALE)
Data Ports Details	(2) USB-A - USB 3.2 Gen 1 (5 Gbps); (4) USB-A - USB 2.0
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
AC Power Adapter Output Specs (V / A)	5V / 4A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.9A; Output: 5V, 4A
DC Barrel Plug	OD: 3.5 x 1.35 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	1.6
CONNECTIONS	
Number of Ports	7
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(2) USB 3.0 A (FEMALE)
Side B - Connector 2	(5) USB A (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green - Power



Powering Business Worldwide

TRIPP LITE
SERIES

CHARGING	
Charging Ports	USB-A: 2A
Charging Ports Details	Dedicated charging port
Charging Ports / Amps	(1) 2A
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	3.00 x 4.60 x 5.50
Shipping Dimensions (hwd / cm)	7.62 x 11.68 x 13.97
Shipping Weight (lbs.)	1.02
Shipping Weight (kg)	0.46
Unit Dimensions (hwd / in.)	0.900 x 4.000 x 2.400
Unit Packaging Type	Box
Unit Weight (lbs.)	0.18
Unit Weight (kg)	0.08
ENVIRONMENTAL	
Operating Temperature Range	-4° to 158°F (-20° to 70°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	5.5 BTU/Hr
Power Provided to Connected Device(s)	5V 0.5A (2.5W) Output (USB-A 2.0), 5V 0.9A (4.5W) Output (USB-A 3.0), 5V 2A (10W) Output (USB 2A Charger)
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	6
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
External Power Supply Certifications	FCC; UL; cUL; RoHS
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	3-year limited warranty
-------------------------------------	-------------------------

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks
are the property of their respective owners.