

USB-C Cable (M/M) - USB 3.2 Gen 1 (5 Gbps), Thunderbolt 3 Compatible, Right-Angle Plug, 1 m (3.3 ft.)

MODEL NUMBER: **U420-01M-RA**



USB cable with right-angle plug connects a smartphone or other USB-C device to the USB-C port on your computer, charger or power bank.

Features

USB-C Cable Connects Devices for Charging, Transferring Data at 5 Gbps Speeds or Viewing 4K Video

This USB cable (M/M) is compatible with any device with a USB-C or Thunderbolt 3 port, including MacBook Pros, Chromebooks and Windows laptops, smartphones and more. It allows you to connect your notebook computer to a docking station, your Apple or Android smartphone to a wall charger or power bank, or an external hard drive to a PC or tablet, to name just a few valuable uses for the cable. It supports USB 3.2 Gen 1 data transfer speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The cable can be used to connect to the USB-C input on a display or travel monitor to transit 4K video from a laptop, tablet or smartphone that supports DisplayPort Alt Mode.

PD Charging Cable Supports up to 60W for Syncing and Charging Mobile Devices

The Power Delivery cable provides power output up to 20V 3A (60W), which is sufficient for fast charging, syncing and powering most smartphones and other mobile devices.

Right-Angle Plug Makes Connecting in Tight Spaces Easier

A space-saving right-angle USB-C connector is easy to install in confined spaces, such as behind your computer or workstation. The right-angle construction also helps relieve strain on the cable and connector and prevents the cable from bending awkwardly.

Reversible USB-C Connectors Attach in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

Specifications

Highlights

- Power Delivery cable supports 20V 3A (60W) power output for charging host device
- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Supports DisplayPort Alt Mode for transmitting 4K video to a connected display
- Space-saving right-angle USB-C plug allows easy connection in confined spaces
- USB-C to USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

Applications

- Charge and power your MacBook Pro, Windows laptop or other USB-C or Thunderbolt 3 device from a USB-C wall charger
- Transfer data between an external hard drive and your laptop or PC
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port

System Requirements

Devices with USB-C or Thunderbolt 3 ports (USB 3.2 Gen 1 compatibility required to achieve USB 3.2 Gen 1 speeds)

Package Includes

U420-01M-RA USB-C to USB-C Cable, M/M, Black, 1 m (3.3 ft.)

OVERVIEW

UPC Code	037332263643
----------	--------------



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	Thunderbolt; USB 3.x
Cable Type	Passive
VIDEO	
Supported Resolutions	3840x4320 (4K); 7680x2160 (8K)
HDR Support	Yes
3D Video Supported	Yes
Signal Transmission	Bidirectional
DisplayPort Alt Mode	Yes
INPUT	
Maximum Input Amps	3
Maximum Input Watts	60
POWER	
USB Power Delivery (PD) Charging Support	Yes
CONNECTIONS	
Side A - Connector 1	USB C (MALE) - RIGHT ANGLE
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Angled
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	3.3
Cable Length (m)	1.01
Cable Length (in.)	39.4
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.03
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Unit Packaging Type	Polybag



Powering Business Worldwide

TRIPP LITE
SERIES

ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	10% to 85% RH, Non-Condensing
Power Provided to Connected Device(s)	60W (20V/3A)
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.