

USB-C to DVI Adapter with USB 3.x (5Gbps) Hub Port and PD Charging, Black

MODEL NUMBER: U444-06N-DUB-C



USB Type-C to DVI adapter adds DVI, USB-A and USB-C PD charging ports to your tablet, laptop, smartphone or PC.

Features

Mini Docking Station Turns Your Device's USB-C or Thunderbolt 3 Port into a Multiport Workstation

This USB Type-C to DVI adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting video to a large display, adding a thumb drive or other USB peripheral, and powering and charging a PD Charging-compliant mobile device—all at the same time.

Supports USB DisplayPort Alternate Mode for Transmitting Video DisplayPort and USB Signals

With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 1080p Video to a DVI Display To send high-definition video to a DVI television, projector or monitor, connect the DVI port to the display using a DVI cable (sold separately). The DVI port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz.

Connects a USB Peripheral The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer. It supports fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and is backward compatible with USB 2.0 and USB 1.1 devices. This dedicated BC 1.2-compliant port provides up to 1.5A of fast-charging power to mobile devices. **Note:** Host must support USB OTG (On-the-Go)

Charges a Connected Device The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the U444-06N-DGUB-C is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W). **Note:** USB-C PD port does not support Quick Charge (QC).

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB-C and Thunderbolt 3 to DVI adapter requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go.

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- BC 1.2-compliant USB-A port provides up to 1.5A of fast-charging power
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

Applications

- Play 1080p video from your laptop or PC on a DVI display
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Transfer files to and from a USB thumb drive or external hard drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DVI input (DVI port)

Package Includes

- U444-06N-DUB-C USB-C to DVI Adapter with USB-A Hub, Thunderbolt 3—1080p, PD Charging, Black, 6 in.
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

3-Year Warranty and Environmentally Responsible DesignThe U444-06N-DUB-C comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting commitment to environmental responsibility.

Specifications

OVERVIEW	
UPC Code	037332209139
Product Type	USB-C to DVI Adapter
Technology	DVI; USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	DVI-I DUAL LINK (FEMALE)
Number of Monitors Supported	1
Video Ports	DVI-I DUAL LINK (FEMALE)
Video Ports Details	HDCP 1.3
Resolutions Supported	1920 x 1080 (1080p) @ 60Hz
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p)
Max Supported Video Resolution	1920 x 1080 (1080p) @ 60Hz
Extended Mode	Yes
Mirror Mode	Yes
3D Video Supported	No
DisplayPort Alt Mode	Yes
DATA	
Data Ports	USB A (FEMALE)
Data Ports Details	USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Built-In Cable Length (ft.)	0.36
Built-In Cable Length (m)	11.0
Built-In Cable Length (in.)	4.33
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5



Powering Business Worldwide

TRIPP LITE
SERIES

Product Length (m)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Consumption (Watts)	1.2
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DVI-I DUAL LINK (FEMALE)
Side B - Connector 2	USB A (FEMALE)
Side B - Connector 3	USB C (FEMALE)
Connector Plating	Nickel
CHARGING	
Total Charging Watts	60
Charging Ports	USB-A: 5V 1.5A (7.5W); USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
Charging Ports Details	x1 20V/3A (60W) PD Charging Port; x1 5V/1.5A (7.5W) USB-A Port
Charging Ports / Amps	1.5A; 3A
PHYSICAL	
Color	Black
Material of Construction	Plastic
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	0.90 x 3.90 x 5.60
Shipping Dimensions (hwd / cm)	2.29 x 9.91 x 14.22
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	0.570 x 3.100 x 1.600
Unit Packaging Type	Box
Unit Weight (lbs.)	0.08
Unit Weight (kg)	0.04



Powering Business Worldwide

TRIPP LITE
SERIES

ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
BTUs	4.1 BTU/Hr
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB-A), Up to 20V 3A (60W) Input (USB-C)
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	1
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
HDCP Specification	1.3
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.