

## 3-Port USB-C Hub - USB 3.x (5Gbps) Hub Ports, Gigabit Ethernet, Thunderbolt 3, 100W PD Charging, Aluminum Housing

MODEL NUMBER: **U460-003-3AGALC**



Adds 3 USB-A ports, PD Charging and Gigabit Ethernet to the USB-C or Thunderbolt 3 port on your MacBook Pro or Windows laptop.

### Features

#### USB 3.2 Hub Connects 3 USB-A Peripherals to Your USB-C Port

This USB-C hub allows you to connect up to three USB peripherals to your MacBook Pro, Windows laptop or other tablet, smartphone or computer with a USB-C or Thunderbolt 3 port. You can expand the capability of your device by connecting USB peripherals that can help you do your job faster, easier and better, such as an external hard drive, keyboard/mouse and printer.

#### Transfers Data at Fast USB 3.2 Gen 1 Speeds

Three USB-A ports transfer data at speeds up to 5 Gbps, and one also supports device charging up to 5V 1.5A (7.5W). The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. **Note:** Host device must support USB OTG (On-the-Go).

#### PD Charging Port Charges Host Device via AC Wall Charger

The USB-C Power Delivery port supports power output up to 20V 5A (100W), which is more than sufficient for charging and powering the connected source device, such as a MacBook Pro, Windows laptop or Chromebook. Just connect the device's wall charger to both the USB-C PD port and an AC outlet. PD 3.0 Fast Role Swap technology ensures the connection remains stable if the wall charger becomes dislodged.

#### Connects to a Wired Gigabit Ethernet Network

The RJ45 port offers access to a Gigabit Ethernet network when Wi-Fi is unavailable or when a wired connection offers faster speeds. Connect using a UTP cable (such as N201-Series Cat6 cables, sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for downloads and web browsing. LEDs indicate at a glance a successful network connection.

#### Ready to Use Right from the Package

The plug-and-play USB-C hub is specifically designed for use with the MacBook Pro, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no drivers or external power. The lightweight aluminum case fits easily into a pocket, briefcase or laptop bag for connecting on the go.

### Highlights

- Bus-powered USB hub is compatible with all USB-C and Thunderbolt 3 devices
- Accepts up to 3 USB peripherals, turning your laptop into a mini workstation
- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- USB-C PD 3.0 port supports 20V 5A (100W) power output for charging host device
- Connects you to a wired 10/100/1000 Ethernet network when Wi-Fi is unavailable

### Applications

- Save data from your computer to a USB thumb drive or external hard drive
- Access a wired Gigabit Ethernet network in a location with no or spotty Wi-Fi
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Connect a USB microphone/headset to record a podcast or listen to music
- Download photos from a digital camera

### System Requirements

- Source device with USB-C or Thunderbolt 3 port (USB 3.2 Gen 1 capability required for 5 Gbps speeds)
- Ethernet network with speeds up to 1000 Mbps (1 Gbps)

### Package Includes

- U460-003-3AGALC 3-Port USB-C Hub
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332264046
Technology	Cat5/5e; Cat6; USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(3) USB A (FEMALE); USB C (FEMALE)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Input Current	5V/1.5A
Built-In Cable Length (ft.)	0.557
Built-In Cable Length (m)	0.17
Built-In Cable Length (in.)	6.69
Product Length (in.)	8.70
Product Length (cm.)	22.1
Product Length (ft.)	0.725
Product Length (m)	0.221
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	100W; 3.0
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB C (MALE)



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	(3) USB C (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Connector Plating	Nickel
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	White (Connection); Orange (Activity)
<b>CHARGING</b>	
Total Charging Watts	100
Charging Ports / Amps	(1) 1.5A; (1) 5A
<b>PHYSICAL</b>	
Color	Gray
Material of Construction	Aluminum
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94
Shipping Weight (lbs.)	0.21
Unit Dimensions (hwd / in.)	3.740 x 1.770 x 0.510
Unit Packaging Type	Box
Unit Weight (lbs.)	0.20
Unit Weight (kg)	0.09
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10 to 85% RH, Non-Condensing
Storage Humidity Range	5 to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	USB-A: 5V/1.5A (7.5W), USB-C: 20V/5A (100W)
<b>COMMUNICATIONS</b>	
Network Compatibility	1 Gbps (Gigabit)
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat5e/6



*Powering Business Worldwide*

TRIPP LITE  
SERIES

**STANDARDS & COMPLIANCE**

TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)

**WARRANTY & SUPPORT**

Product Warranty Period (Worldwide)	3-year limited warranty
-------------------------------------	-------------------------

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.