

Industrial Power Strip, 6-Outlet, 15 ft. (4.6 m) Cord, Locking Switch Cover

MODEL NUMBER: **UL24CB-15**

Highlights

- 6 outlets
- 15-ft. (4.57 m) cord
- 12.5" length
- All metal housing
- Lighted master switch

Package Includes

- UL24CB-15 Power Strip
- Warranty information
- Instruction manual

Description

The UL24CB-15 Power Strip offers a convenient method of power distribution in workbench, wall-mount or floor-mount applications. Includes six NEMA 5-15R outlets with 1.625-inch center-to-center spacing, 15-foot (4.6-meter) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL24CB-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15A resettable circuit breaker and attractive blue/gray color scheme.

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.625 inch center-to-center outlet spacing
- Lighted power switch with transparent snap-over guard to prevent accidental shutoff
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity with circuit breaker
- 15-ft. (4.57 m) AC line cord

Specifications

OVERVIEW	
UPC Code	037332115546
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V



Powering Business Worldwide

TRIPP LITE
SERIES

Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
Outlet Spacing	1.625 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Gray
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Blue; Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	261.92mm
Outlets Measurement (Center to Center)	1.62 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	14.10 x 2.25 x 6.00
Shipping Dimensions (hwd / cm)	35.81 x 5.72 x 15.24
Shipping Weight (lbs.)	3.20
Shipping Weight (kg)	1.45
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Outlet Spacing	1.625 in.
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.