

Industrial Power Strip, 10-Outlet, 15 ft. (4.6 m) Cord, Large Plug Spacing

MODEL NUMBER: **UL800CB-15**



Highlights

- 10 outlets
- 15-ft. (4.57 m) cord
- 17.5" length
- Lighted master switch
- All metal housing

Package Includes

- UL800CB-15 Power Strip
- Warranty information
- Instruction manual

Description

The UL800CB-15 Power Strip offers a reliable, convenient method of power distribution for appliances, power tools, lighting and other electrical equipment. Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage. Includes 15-foot (4.6-meter) AC line cord and flat sheet metal flanges for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL800CB-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch, 15A resettable circuit breaker and attractive blue/gray color scheme.

Features

- Multi-outlet power strip offers reliable, convenient, cost effective method of power distribution for appliances, power tools, lighting and other electrical equipment.
- Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage
- Lighted on/off switch controls power to all outlets
- Keyhole mounting tabs for installation in a wide variety of applications
- UL Recognized Component, Tested to UL1363 (Power Tap), cUL (Canada)
- 15 amp power handling capacity with circuit breaker
- 15-ft. (4.57 m) AC line cord

Specifications

OVERVIEW	
UPC Code	037332117724
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Powering Business Worldwide

TRIPP LITE
SERIES

Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(5) Yes
Outlet Orientation	Two rows of 5 outlets
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Blue; Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between end tabs = 462.30mm
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 2.81 in.; Distance between vertical outlets = 1.53 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.50 x 9.00 x 20.25
Shipping Dimensions (hwd / cm)	6.35 x 22.86 x 51.44
Shipping Weight (lbs.)	5.15
Shipping Weight (kg)	2.34
Unit Dimensions (hwd / in.)	2.250 x 17.500 x 4.000
Unit Dimensions (hwd / cm)	44.5 x 10.2 x 4.4



Powering Business Worldwide

TRIPP LITE
SERIES

Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.