

Universal Reversible USB 2.0 Cable (Reversible A to 5Pin Micro B M/M), 6-in. (15.24 cm)

MODEL NUMBER: **UR050-06N**



Universal / Reversible "A" connector allows plugging in any direction

Features

- USB Universal / Reversible A Male to Micro-B Male
- Available in lengths up to 10-ft. (3.05 m)
- 480Mbps USB 2.0 Data Transfer Rates
- Data and Power transference

Specifications

OVERVIEW	
UPC Code	037332182302
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
Connector Style	Straight
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15

Highlights

- Next Generation USB Digital Device Connector
- Provides both Data and Power transfers
- USB 2.0 480Mbps Transfer rates
- Universal / Reversible "A" Male to Micro-B Male

System Requirements

- Digital devices that use the USB Micro-B Female socket

Package Includes

- 6-in. USB2.0 Universal / Reversible A to Micro-USB B Device Cable (A Male to Micro-B Male)



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	0.25 x 0.25 x 6.00
Shipping Dimensions (hwd / cm)	0.64 x 0.64 x 15.24
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Storage Elevation (ft.)	-20/+80° C (-4 to 176° F)
Storage Elevation (m)	-20/+80° C
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.