

## Adjustable-Height Wall-Mount Sit-Stand Workstation, Single-Display

MODEL NUMBER: **WWSS1327RWTC**



Sit-stand workstation transforms your desk space into an ergonomic working environment without modifying the surface.

### Features

**Enjoy the Benefits of Standing During Your Workday** This WorkWise™ sit-stand workstation mounts to the wall using the included hardware, allowing you to enjoy the benefits of better workplace ergonomics. Standing for part of the day can help increase metabolism, improve alertness and productivity, reduce fatigue and decrease the risk of repetitive stress injuries. Ideal for home, school or office use, the WWSS1327RWTC lets you sit or stand with 28.7 inches of single-motion height extension.

**Easy to Adjust to Your Liking** The keyboard and monitor are attached to separate arms, so you can adjust them independently to accommodate your perfect set. You can rotate the monitor 360 degrees for viewing in portrait or landscape orientation. The monitor also swivels -90° to +90° and tilts -15° to +15° for the perfect viewing angle. Increase or decrease tension in both arms using the included hex key to compensate for heavier or lighter loads. The keyboard arm and tray fold up to save space when not in use.

**VESA-Compliant Mount Supports Monitor and Keyboard Up to 18 lb.** The VESA-compliant mount fits most flat-panel monitors, televisions and other displays from 13 to 27 inches. It's compatible with 75 x 75 mm and 100 x 100 mm VESA mounting-hole patterns. Mount supports up to 12.5 pounds. The thin-client bracket and the keyboard arm each support up to 2.5 pounds.

**Integrated Thin-Client Mount and Cable Management** By integrating your thin client into your display mount set, you can create a complete system right at your fingertips. The thin-client bracket mounts directly behind the monitor. Cable managers cut down on workspace clutter.

## Specifications

OVERVIEW	
UPC Code	037332210906
Device Compatibility	Monitor/HDTV; Computer; Laptop

### Highlights

- Mounts firmly to wall to leave valuable desk or table space clear
- Adjusts to fit wide range of flat-screen monitors from 13 to 27 in.
- Thin-client mount integrates a small CPU into your display mount configuration
- Monitor swivels from -90° to +90° and rotates 360° to customize the ideal viewing angle
- Includes necessary mounting hardware so you can start installation immediately

### Package Includes

- Display arm
- (2) Keyboard arms
- Thin-client bracket
- Keyboard tray
- Wall rail
- Keyboard tray holder
- Keyboard arm attachment
- Mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

PHYSICAL	
Color	Black; Silver
Material of Construction	Steel, Plastic
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; -90/+90 Swivel; 360 Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	17.5
Maximum Weight Capacity (kg)	8
Number of Displays	1
Unit Dimensions (hwd / in.)	28.700 x 23.600 x 34.800
Unit Dimensions (hwd / cm)	72.9 x 59.94 x 83.39
Unit Weight (lbs.)	11.50
Unit Weight (kg)	5.22
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.