



Quality Products. Service Excellence.

Miniature Audio Epoxy Potted 104 Series
PC Board Mount

Features



- Output power models from 5 to 1,500 milliwatt level available.
- P.C. board mount - square pin type (0.025" square typical)
- Bifilar winding technique used on center tapped units for balanced resistive and capacitive characteristics.
- Rugged black epoxy potted construction produces a completely sealed unit withstanding severe environmental conditions including those of MIL-T-27 (Grade 5, Class S).
- For the more economical open type P.C. mount types please refer to the 148 and 149 series.
- Peak working voltage rating of: 200V
- Referring to figures 1-9, if connection is not used - no pin will exist.
- Pin length is 0.11" +/-15%



Gallery



Part No.	Typical Applicaton	Nominal Impedance (Ohms)		Max. Primary D.C. ma. (*1)	D.C. Resistance (Ohms) +/- 15%		Output Milliwatts (*2)	Insertion Loss db (*3)	Low Frequency Roll Off -1 db (Hz.) (*4)	Drawing Figure
		Primary	Secondary		Primary	Secondary				
104B	Input	150	80000	0	6.6	3730	5	1	60	5
104H	Interstage	10000	2,000 ct	3.2	675	89	35	1	200	6
104K	Interstage	20000	1,000 ct	3.2	790	125	35	1	200	6
104L	Interstage	25000	600 ct	2	1890	50	35	1	200	6
104Q	Output	500 ct	3.2	6	27	0.4	500	1	200	3
104R	Output	500 ct	8	6	27	0.9	500	1	200	3
104S	Output	600 ct	150 ct	6	47	10.6	500	1	200	4
104SL	Output	600 ct	150 ct	6	46	10.3	500	1	200	SEE DWG

Tags: audio transformer, potted, miniature, PCB mount, epoxy, interstage, input, output, bifilar winding

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.