



Quality Products. Service Excellence.


500mw Audio Miniature Epoxy Potted 108 Series

PC Board Mount

Features



- Perfect for audio input, line matching, isolation or output transformer applications.
- 500 milliwatt (+/- 1.5 db, 300 Hz. - 50 KHz.).
- Epoxy potted in an attractive black molded case, Pin type P.C. board mount (min. 0.187" length).
- In some models where no center tap is required (on secondary), pin No. 5 is omitted.
- Power level ratings are maximum at lowest frequency rating (see charts & PDF spec. sheets below)
- Power can be increased slightly at higher frequencies. See individual PDF specs. for specifics.
- Will withstand soldering for 10 sec. @ 260 degrees C, ambient temp. 85 degrees C max.



Part No.	Nominal Impedance (Ohms)		D.C. Resistance (Ohms) +/- 20%		Max. D.C. Unbalance (ma.)
	Primary (Pins 1-3)	Secondary (Pins 4-6)	Primary (Pins 1-3)	Secondary (Pins 4-6)	
108E	600 ct	3.2	65	0.43	6
108F	600 ct	150 ct	65	18	6
108G	600 ct	250 ct	65	29	6
108H	600 ct	600 ct	65	69	6
108J	1K ct	600 ct	109	69	4.5
108K	1.5K ct	600 ct	170	69	4
108L	10K ct	3.2	1050	0.43	1.5
108N	10K ct	600 ct	1050	69	1.5
108P	10K ct	1.5K ct	1050	180	1.5
108T	10K ct	10K ct	1050	1200	1.5

Tags: audio transformer, potted, miniature, PCB mount, epoxy, input, output, line matching, isolation *Data subject to change without notice*

