



Quality Products. Service Excellence.

## Type 4X Stainless Steel Freestanding Enclosure 1418 N4 FS QT SS Series

Continuous Hinge Door with Quarter Turn



### Application

- Designed to house electrical, electronic, hydraulic or pneumatic controls with provision for panel mounting or rack mounting of equipment.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.
- A variety of inner panels, rack mounting rails and swing out frames are available to provide flexibility in mounting arrangements.

### Standards

- UL 508A Type 3R, 4, 4X and 12
- CSA Type 3R, 4, 4X and 12
- Complies with
  - NEMA Type 3R, 4, 4X, 12 and 13
  - IEC 60529, IP66

### Construction



- Formed 12 gauge 304 or 316 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Heavy duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges.
- Doors are secured with quarter turn latches.
- Seamless poured-in place gasket.
- Mounting channels are welded on the inside of the enclosure for mounting of optional inner panels or rack equipment rails.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.

### Finish

- Cover and enclosure are natural stainless steel with a smooth brushed finish.
- Optional inner panels are finished in white powder paint.

### Accessories

<ul style="list-style-type: none"> <li>Inner Panels</li> <li>Swing Out Frames</li> <li>Drip Shield Kit</li> <li>Climate Control</li> <li>Lighting</li> </ul>	<ul style="list-style-type: none"> <li>Panel Rails</li> <li>Door Stop Kit</li> <li>Quarter Turn Inserts and Keys</li> <li>Window Kits</li> <li>General Accessories</li> </ul>
--	---

**New and improved PDF part  
drawing files with more detail  
now available.**

Click part number in table below  
to access PDF, DXF, and STEP files.

304 S.S.	316 S.S.	Enclosure			Optional Full Size
Part No.	Part No.	H	W	D	Inner Pannel
1418N4SSW18QT	1418N4S16W18QT	72.06	25.06	18.06	72WFW
1418N4SSX24QT	1418N4S16X24QT	72.06	31.06	24.06	72XFW
1418N4SSY24QT	1418N4S16Y24QT	72.06	37.06	24.06	72YFW

Alternative inner panel options also available.

Tags: **1418, freestanding, stainless, stainless steel, 304, 316, control box, Type 4X, NEMA 4X, continuous hinge, quarter turn**

*Data subject to change without notice*

© 2025. Hammond Manufacturing Ltd. All rights reserved.