



Quality Products. Service Excellence.

Soft Grip Cabinet Caster Set 1425BL Series

660 lbs (299 kg) Weight Capacity



Features

- Unique soft tread design ideal for medical, office and institutional environments.
- Twin wheels increase ease of swivel for added maneuverability.
- Quiet and non-marking thermoplastic elastomer wheel treads provide floor protection.
- All casters include peddle lock.
- Includes mounting hardware.
- Grey finish with plated zinc top plate and stem.
- RoHS and REACH Compliant.

Compatibility



- C2/C2RR | Equipment Cabinet
- C4/C4RR | Server Cabinet
- DNRRRLDK | 2-Post Open Frame Rack
- SDC | Low-Profile Server Cabinet
- RCK | Knockdown Equipment Cabinet
- RCSC | Knockdown Server Cabinet

Part No.	Strength	Wheel Diameter	Overall Height		Caster Set		Qty	
			Added to Cabinet	Width	Hole Mounting Pattern	Weight Capacity	In Set	Brakes Included
1425BL	Light Duty	2.95	3.50	1.75	3.00	660 lbs (299 kg)	4	Yes

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.