



Quality Products. Service Excellence.

Type 12 Mild Steel Junction Box 1436/1438 Series

Lift-Off Cover with Screws



Application

- Designed for use as instrument enclosures, electrical junction boxes or terminal wiring enclosures.
- Provides a degree of protection from falling dirt, dust, oil and water.

Standards

- UL 508A Type 12 and 13
- CSA Type 12 and 13
- Complies with
 - NEMA Type 12 and 13
 - IEC 60529, IP54

Construction

- Formed from 16 gauge steel.
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Welded brackets provide for enclosure mounting.
- Lift off cover is secured with captive, plated steel screws, and supported on internal hinges except as noted on charts at bottom and left.
- Cover screws fasten into threaded, sealed wells.
- Oil resistant gaskets are permanently secured.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray recoatable powder coating.

Accessories

- General Accessories

Standard Depth Series (1436)

Part No.	H	Enclosure	
		W	D
1436A ¹	3.50	3.25	2.75
1436B ¹	5.75	3.25	2.75
1436C ¹	8.00	3.25	2.75
1436D ¹	10.25	3.25	2.75
1436F	7.25	6.25	3.00
1436H	9.50	6.25	3.00
1436K	9.50	8.50	3.00
1436O	11.75	8.50	3.00
1436S	11.75	10.75	3.00

Part No.	Enclosure		
	H	W	D
1436V	14.00	10.75	3.00

¹ Not hinged

Extra Deep Series (1438)

Part No.	Enclosure		
	H	W	D
1438A ¹	4.00	4.00	4.75
1438B	6.00	4.00	4.75
1438C	8.00	4.00	4.75
1438D	10.00	4.00	4.75
1438F	7.25	6.25	4.75
1438H	9.50	6.25	4.75
1438K	9.50	8.50	4.75
1438O	11.75	8.50	4.75
1438S	11.75	10.75	4.75
1438V	14.00	10.75	4.75

¹ Not hinged

Tags: 1436, 1438, junction box, terminal box, electric, mild steel, Type 12, Type 13, NEMA 12, NEMA 13, *Data subject to change without notice*
lift off cover, screws

© 2025. Hammond Manufacturing Ltd. All rights reserved.