



Quality Products. Service Excellence.

1U Rack Mount PDU with Individual Switches 1583-9W Series

Features



- Individually switched receptacles help eliminate Phantom Power and provides easy power control over connected devices.
- 1U horizontal 19" rackmount installation.
- 15A models include illuminated on/off rocker switches while the 20A models include an red plastic inlay indicator.
- Plug types are available in:
 - NEMA 5-15P and 5-20P straight blade
 - NEMA L5-15P and L5-20P locking type
- Includes four (4) rubber feet should you wish not to rack mount the product.

Specifications



- Heavy duty corded plug:
 - 15A models have a 14 gauge wire corded plug – 14/3 SJT type
 - 20A models have a 12 gauge wire corded plug – 12/3 SJT type
- Includes 125 VAC circuit breaker to prevent accidental overload.
- UL/cUL recognized to standards UL1363 & CSA C22.2 No.308.
- Finished in RAL9005 black powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America.

On/Off Switch	Overall Dimensions			Rear Outlets	NEMA Type		Cord Length	Plug Type
Part No.	Height	Width	Depth	Outlet	Plug			
1583W8A1BK	1.72	19.00	3.66	8	5-15R	5-15P	6 ft	Straight
1583W8B1BK	1.72	19.00	3.66	8	5-15R	5-15P	15 ft	Straight
1589W8F1BKRR	1.72	19.00	3.66	8	5-20R	5-20P	6 ft	Straight
1589W8G1BKRR	1.72	19.00	3.66	8	5-20R	5-20P	15 ft	Straight

Tags: w/Individual Switches, Individual Outlet On/Off Switches

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.