



Quality Products. Service Excellence.

## Type 1 Mild Steel Metering Cabinets CMC Series

Hinge Door with Quarter Turn



### Application

- Designed for indoor housing of metering transformers.

### Standards

- CSA Type 1
- Complies with
  - NEMA Type 1
  - IEC 60529, IP20

### Construction

- Formed and spot welded from 14 or 16 gauge steel.
- Spot welded construction and formed edges.
- Removable inner panel.
- Single and Double Door versions
- Hinged covers - single door with hasp closure, double door with hasp and quarter turn closure.
- 2 cutouts in top of each cabinet with metering plates included (except 27x13x10")



### Finish

- Enclosure and cover are finished in ANSI 61 gray inside and out.
- Inner panel is finished in white powder coating



**New and improved PDF part drawing files with more detail now available.**

Click part number in table below to access PDF, DXF, and STEP files.

Part No.	Type of Door	Enclosure			Inner Panel	
		H	W	D	H	W
CMC202010	Single	20.00	20.00	10.00	16.00	16.00
CMC271310*	Single	27.00	13.00	10.00	23.00	9.00
CMC302010	Single	30.00	20.00	10.00	26.00	16.00
CMC303010	Double	30.00	30.00	10.00	26.00	26.00
CMC363612	Double	36.00	36.00	12.00	32.00	32.00
CMC484812	Double	48.00	48.00	12.00	44.00	44.00

\* No cutouts in top or metering plates

© 2026. Hammond Manufacturing Ltd. All rights reserved.