



Quality Products. Service Excellence.

Type 1 Mild Steel Metering Cabinets - UG Style CMCUG Series

Hinge Door with Quarter Turn

NEW



Application

- Designed for housing of metering transformers. in underground situations

Standards

- CSA Type 1
- Complies with
 - NEMA Type 1
 - IEC 60529, IP20

Construction

- Formed and spot welded from 14 or 16 gauge steel.
- Spot welded construction and formed edges.
- Single and Double Door versions
- Hinged covers - single door with hasp closure, double door with hasp and quarter turn closure.



Finish

- Enclosure and cover are finished in ANSI 61 gray inside and out.

Gallery



Part No.	Type of Door	Enclosure		
	H	W	D	
CMC202010UG	Single	20.00	20.00	10.00
CMC303010UG	Double	30.00	30.00	10.00
CMC363612UG	Double	36.00	36.00	12.00
CMC484812UG	Double	48.00	48.00	12.00

Tags: CMC, metering, type 1, steel, indoor, single door, double door

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.