

*Quality Products. Service Excellence.*

Adjustable Rack Shelf DNRMA Series

Load rated to 275 lbs (125 kg)

Features



- 14-Gauge steel construction.
- Movable side brackets allow mounting inside or outside rack at 4 different depths
- Designed mainly for open relay racks - works panel mounted on any rack
- Choice of 16-inch or 20-inch deep.
- Available in either 19-inch rack panel width
- Knockdown design ships unassembled for easy handling and shipping protection.
- 275 lbs (125 kg) **load rating**.
- Finished in rugged textured RAL9005 black powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS and REACH compliant.
- Manufactured in North America.

Accessories

- Hardware for Rack Mounting Solutions
- Rack Rail Reducer Panel





Part No.	Mounting Width	Overall Depth	Rack Units	Mounting Height
DNRMA1916BK1	19.00	16.00	3U	5.25
DNRMA1920BK1	19.00	20.00	3U	5.25

Tags: **adjustable server rack shelf**

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.