



Quality Products. Service Excellence.

Type 4 Two Door Freestanding Enclosure *HN4 FSTD Series*

Continuous Hinge Door with Handle



**Panel
Sold
Separately**



Application

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications.

Construction

- Formed 12 gauge steel.
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Heavy duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges.
- Dual Access versions have doors front and back.
- 3-pt padlocking door handle.
- Seamless poured-in place gasket.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- Center post is removable for easy installation of the inner panel.

Standards

- UL 508A Type 3R, 4 and 12
- CSA Type 3R, 4 and 12
- Complies with:
 - NEMA Type 3R, 4, 12 and 13
 - IEC 60529, IP66

Finish

- Cover and enclosure are finished in recoatable smooth ANSI 61 gray powder coating.
- Optional inner panels are available in white powder coating, or unpainted galvanized steel.

Accessories

- Inner Panels
- Panel Rails
- Door Stop Kit
- Drip Shield Kit
- Window Kits
- Lighting
- Center Panel Supports
- Swing Out Frames
- Top Hat Cable Modules
- Type 12/4, 4X Handle Kits
- Climate Control
- General Accessories

Single Access

Part No.	Enclosure			Optional Full Panel ¹
	H	W	D	
HN4FS604818	60.00	48.00	18.00	60AWFW
HN4FS724818	72.00	48.00	18.00	72ZWFW

Enclosure				Optional
Part No.	H	W	D	Full Panel ¹
HN4FS726018	72.00	60.00	18.00	72ZXFW
HN4FS727218	72.00	72.00	18.00	72ZYFW
HN4FS904820	90.00	48.00	20.00	90BWFW
HN4FS907220	90.00	72.00	20.00	90BYFW
HN4FS724824	72.00	48.00	24.00	72ZWFW
HN4FS726024	72.00	60.00	24.00	72ZXFW
HN4FS727224	72.00	72.00	24.00	72ZYFW
HN4FS907224	90.00	72.00	24.00	90BYFW
HN4FS726036	72.00	60.00	36.00	72ZXFW
HN4FS907236	90.00	72.00	36.00	90BYFW

¹ Refers to optional full height/full width panels. Depth panels/half height width panels are also available

Dual Access

Enclosure				Optional
Part No.	H	W	D	Full Panel ¹
HN4FS724824DA	72.00	48.00	24.00	72ZWFW
HN4FS726024DA	72.00	60.00	24.00	72ZXFW
HN4FS727224DA	72.00	72.00	24.00	72ZYFW
HN4FS907224DA	90.00	72.00	24.00	90BYFW
HN4FS726036DA	72.00	60.00	36.00	72ZXFW

¹ Refers to optional full height/full width panels. Depth panels/half height width panels are also available

Tags: **HN4FS, freestanding, steel, type 4, NEMA 4, single access, dual access, outdoor, continuous hinge, handle**

Data subject to change without notice