



Quality Products. Service Excellence.

## Heavy-Duty Swing-Out Wall Mount Cabinet HWM Series

UL2416 rated to 350 lbs (158 kg). Seismic rated up to 200 lbs (90.72 kg).

**Note:** This product line will be discontinued on April 14, 2026 at which time it will only be available while supplies last. No returns will be possible after the discontinuation date.

**!** The suggested replacement will be **HWC Series**. For alternative solution assistance, please [contact Hammond here](#) or call: USA (716) 630-7030, Canada and International (519) 822-2960.



**Note:** We are consolidating our swing-cabinet portfolio in April 2026. The HWM will be replaced by the HWC, which will be updated with a rear-panel design matching the HWM. Additional features are slated for rollout in the coming months.

The HWM Wall-Mount Cabinet offers a secure, swing-out storage solution for ICT equipment that is easy to install. With its sleek design, security features, and optional fan kits, it is perfect for public spaces or equipment rooms with limited floor space.

### Features

- Available in two (2) depths and four (4) heights.
- Available with either a locking vented 63% perforated front door or a locking **acrylic window** front door.
- Heavy-duty spring-hinge pin for easy installation and removal.
- Body can be installed to swing from left to right or right to left.
- Each cabinet side includes six (6) fan grills allowing for active airflow as required.
- Rear section features:
  - The side of the rear section includes 2.50" and 2.00" knockouts.
  - The top and bottom of the rear section include 3.00", 2.00", 1.38", and 1.12" knockouts.
  - Generous cable management lances are located on the rear section and mounting rails.
  - Mounting points for outlet strips.
  - Heavy-duty keyhole for wall mounting.
  - Large opening in the rear for cable access. NOTE: Pole mounting requires a back plate (sold separately - see tables for part info).
- The front locking door and center section are keyed the same (optional secondary key available to provide additional security).
- Includes one (1) pair of 10-32 threaded rack rails with support for additional optional rails (see accessory table).
- Starter pack of **SCREW1032-50** screws.



Rack Mounting Hardware Included



### Specifications

- 14-gauge welded rear section; 16-gauge center section and doors.
- EIA-compliant adjustable depth mounting rails.
- Grounding lugs are located on the top and bottom of the door, center, and rear sections.
- **UL Listed 2416 load rated to 350 lbs (158 kg).**



- Wall Mount Racks are rated based on cabinet's weight plus the desired weight capacity to a two (2x) multiplier. 200lbs (Cabinet Weight) + 350lbs (Cabinet Load Capacity) x 2 = 1,100. In this case, the Static Load is 1,100 lbs, and the UL2416 Load Rating is 350lbs.
- Seismic rated up to 200 lbs (90.72 kg) of dynamic load with an Ip factor of 1.5 in accordance with the IBC 2018, CBC 2019, NBC 2018, ASCE 7-16, and ASCE 7-10.
- Finished in sand-textured RAL9005 black or textured RAL9003 white powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

## Gallery



## Accessories

- Vertical Cable Tray
- Horizontal Hinged Cable Manager
- Universal Rack Shelf
- Magnet Panel Cover
- Heavy Duty Cooling Fan Kits
- Hardware for Rack Mounting Solutions
- Padlock Adaptor
- Rack Panels
- Horizontal Lacing Strip
- Clamping Rack Shelf
- Rack Unit Label
- Bonding and Grounding
- We Manufacture PDUs and Outlet Strips



## Vented Door

| Part No.      | Part No.      | Overall Dimensions |       |       | Center Section | Rack  | Mounting (Usable) Dimensions |       |       | Alternative |
|---------------|---------------|--------------------|-------|-------|----------------|-------|------------------------------|-------|-------|-------------|
| RAL9005 Black | RAL9003 White | Height             | Width | Depth | Depth          | Units | Height                       | Width | Depth | Part No.    |
| HWM2412U20BK  | HWM2412U20WH  | 27.75              | 24.68 | 25.18 | 20             | 12U   | 21.00                        | 19.00 | 22.85 | RB-SW12DV   |
| HWM2412U26BK  | HWM2412U26WH  | 27.75              | 24.68 | 31.18 | 26             | 12U   | 21.00                        | 19.00 | 28.85 | RB-SW12DV   |
| HWM2420U20BK  | HWM2420U20WH  | 41.75              | 24.68 | 25.18 | 20             | 20U   | 35.00                        | 19.00 | 22.85 | RB-SW18DV   |
| HWM2420U26BK  | HWM2420U26WH  | 41.75              | 24.68 | 31.18 | 26             | 20U   | 35.00                        | 19.00 | 28.85 | RB-SW18DV   |
| HWM2424U20BK  | HWM2424U20WH  | 48.75              | 24.68 | 25.18 | 20             | 24U   | 42.00                        | 19.00 | 22.85 | -           |
| HWM2424U26BK  | HWM2424U26WH  | 48.75              | 24.68 | 31.18 | 26             | 24U   | 42.00                        | 19.00 | 28.85 | -           |
| HWM2432U20BK  | HWM2432U20WH  | 62.75              | 24.68 | 25.18 | 20             | 32U   | 56.00                        | 19.00 | 22.85 | -           |
| HWM2432U26BK  | HWM2432U26WH  | 62.75              | 24.68 | 31.18 | 26             | 32U   | 56.00                        | 19.00 | 28.85 | -           |

Old Style O/A Depth of 25.70" and 31.70" Note: Mounting Dimensions / Usable Depth is the maximum equipment depth that will allow the body section of the cabinet to swing out unimpeded.

## Window Door

| Part No.       | Part No.       | Overall Dimensions |       |       | Center Section | Rack  | Mounting (Usable) Dimensions |       |       |
|----------------|----------------|--------------------|-------|-------|----------------|-------|------------------------------|-------|-------|
| RAL9005 Black  | RAL9003 White  | Height             | Width | Depth | Depth          | Units | Height                       | Width | Depth |
| HWM2412U20WDBK | HWM2412U20WDWH | 27.81              | 24.68 | 25.17 | 20             | 12U   | 21.00                        | 19.00 | 22.85 |
| HWM2412U26WDBK | HWM2412U26WDWH | 27.81              | 24.68 | 31.18 | 26             | 12U   | 21.00                        | 19.00 | 28.85 |
| HWM2420U20WDBK | HWM2420U20WDWH | 41.81              | 24.68 | 25.17 | 20             | 20U   | 35.00                        | 19.00 | 22.85 |
| HWM2420U26WDBK | HWM2420U26WDWH | 41.81              | 24.68 | 31.18 | 26             | 20U   | 35.00                        | 19.00 | 28.85 |
| HWM2424U20WDBK | HWM2424U20WDWH | 48.81              | 24.68 | 25.17 | 20             | 24U   | 42.00                        | 19.00 | 22.85 |
| HWM2424U26WDBK | HWM2424U26WDWH | 48.81              | 24.68 | 31.18 | 26             | 24U   | 42.00                        | 19.00 | 28.85 |
| HWM2432U20WDBK | HWM2432U20WDWH | 62.81              | 24.68 | 25.17 | 20             | 32U   | 56.00                        | 19.00 | 22.85 |

| Part No.       | Part No.       | Overall Dimensions |       |       | Center Section | Rack  | Mounting (Usable) Dimensions |       |       |
|----------------|----------------|--------------------|-------|-------|----------------|-------|------------------------------|-------|-------|
| RAL9005 Black  | RAL9003 White  | Height             | Width | Depth | Depth          | Units | Height                       | Width | Depth |
| HWM2432U26WDBK | HWM2432U26WDWH | 62.81              | 24.68 | 31.18 | 26             | 32U   | 56.00                        | 19.00 | 28.85 |

Old Style O/A Depth of 25.70" and 31.70" Note: Mounting Dimensions / Usable Depth is the maximum equipment depth that will allow the body section of the cabinet to swing out unimpeded.

## Accessories

| Cabinet<br>Rack Units | Rear-Pan Panel<br>for Post Mounting | Tapped 10-32<br>Rail (Pair) | Square Hole<br>Rail (Pair) | Vertical Cable Manager |
|-----------------------|-------------------------------------|-----------------------------|----------------------------|------------------------|
| 12U                   | HWMRPP12                            | HWMTR12U                    | HWMSR12U                   | -                      |
| 20U                   | HWMRPP20                            | HWMTR20U                    | HWMSR20U                   | -                      |
| 24U                   | HWMRPP24                            | HWMTR24U                    | HWMSR24U                   | VCT42                  |
| 32U                   | HWMRPP32                            | HWMTR32U                    | HWMSR32U                   | VCT56                  |

## Optional Front Door Replacement Lock

Part No.

HWMSLOCK

As both the front door and rear section are keyed alike, the HWMSLOCK replaces the existing door lock. This is ideal if you are installing the rack, and you want to prevent others from messing up your hard work.

## Optional Inner Panel

| Part No.            | Part No.            | Cabinet    | Overall Dimensions |       |       |
|---------------------|---------------------|------------|--------------------|-------|-------|
| Steel RAL9003 White | Aluminum Unfinished | Rack Units | Height             | Width | Depth |
| WRPS12UWH           | WRPS12UNF           | 12U        | 16.63              | 16.19 | 0.50  |
| WRPS20UWH           | WRPS20UNF           | 20U        | 30.63              | 16.19 | 0.50  |
| WRPS24UWH           | WRPS24UNF           | 24U        | 37.63              | 16.19 | 0.50  |
| WRPS32UWH           | WRPS32UNF           | 32U        | 51.63              | 16.19 | 0.50  |

Tags: **Sectional Wall Mount Rack, Pivoting Rack, Data Wall Cabinet, Dual Hinge, Hinged Swing Gate, Edge Computing, DWR, Pivoting Wall Rack, Intermediate Distribution Frame (IDF), IT Cube, wall mounted data cabinet**

*Data subject to change without notice*

© 2026. Hammond Manufacturing Ltd. All rights reserved.