



Quality Products. Service Excellence.

Swing-Out Wall Mount Cabinet RB-SW Series

Load rated to 130 lbs (59 kg)



Features:

- Double-hinged for easy rear access (body swings open to 120°).
- Constructed in light-duty 16-gauge steel.
- Includes two (2) pairs of EIA compliant square hole punched rails with 19" mounting.
 - Starter pack of (25) M6 screws and cage nuts included.
 - For 10-32 hardware, see our **CAGKIT Series**.
- Rails are adjustable.
- Includes one (1) locking tempered glass reversible front door (hinged on the right side as standard).
- Includes one (1) pair of locking removable side panels.
- The front and side of the frame include venting for airflow.
- Top, bottom and rear cable access.
- Provision for optional fans on the top panel.
- The middle body section is not reversible and hinges on the left side.
- Ships assembled - ready to install.
- Meets PCI DSS (Payment Card Industry Data Security Standard) compliance requirements.
- Finished in black powder paint.
- 130 lbs (59 kg) of equipment load capacity.
- RoHS Compliant.



RACK BASICS®

A HAMMOND BRAND

Part of the Rack Basics® line of value rack solutions.

Accessories

- Horizontal Ring Cable Manager
- Cable Lacing Bar
- Heavy Duty Cooling Fan Kits
- We Manufacture PDUs and Outlet Strips
- Horizontal Lacing Strip
- Universal Rack Shelf
- Hardware for Rack Mounting Solutions



 Rack Mounting Hardware Included



Electronic Industries Alliance





Part No.	Overall Dimensions			Rack		Mounting Dimensions	
	Height	Width	Depth	Units	Height	Width	Depth
RB-SW9	19.90	23.62	21.65	9U	15.75	19.00	16.13
RB-SW12	25.15	23.62	21.65	12U	21.00	19.00	16.13
RB-SW15	30.40	23.62	21.65	15U	26.25	19.00	16.13
RB-SW18	35.65	23.62	21.65	18U	31.50	19.00	16.13

Note: Mounting Dimensions / Usable Depth is the maximum equipment depth that will allow the center section of the cabinet to swing out unimpeded.

Tags: **Pivoting Wall Rack**

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.