



Quality Products. Service Excellence.

Swing-Out Wall Mount Cabinet RB-SWDV Series

Load rated to 200 lbs (90.72 kg)



Features:

- Double-hinged for easy rear access.
- Constructed in light-duty 16-gauge steel.
- Includes two (2) pairs of EIA compliant square hole punched rails with 19" mounting.
 - Starter pack of (25) M6 screws and cage nuts included.
 - For 10-32 hardware, see our **CAGKIT Series**.
- Rails are adjustable.
- Includes one (1) locking vented door.
- Includes one (1) pair of vented locking removable side panels.
- Top, bottom and rear cable access.
- Includes fan vents for **optional fans** as well as holes for **optional casters** on the top and bottom.
- The entire cabinet can be flipped 180 degrees to accommodate hinging right-to-left.
- Ships assembled - ready to install.
- Meets PCI DSS (Payment Card Industry Data Security Standard) compliance requirements.
- 200 lbs (90.72 kg) of equipment load capacity.
- Finished in black powder paint.
- RoHS Compliant.

RACK BASICS®

A HAMMOND BRAND



 Rack Mounting
Hardware Included



Part of the Rack Basics® line of value rack solutions.

Gallery



Accessories

• Horizontal Ring Cable Manager	• Horizontal Lacing Strip
• Cable Lacing Bar	• Universal Rack Shelf
• Heavy Duty Cooling Fan Kits	• Hardware for Rack Mounting Solutions
• 1U Rack Mount PDU with Individual Switches	• Rack and Cabinet Caster Set



Part No.	Swing-Out Overall Dimensions			Rack Units	Mounting Dimensions		
	Vented	Height	Width		Depth	Height	Width
RB-SW12DV		25.50	23.62	25.59	12U	21.00	19.00
RB-SW15DV		30.40	23.62	25.59	15U	26.25	19.00
RB-SW18DV		35.70	23.62	25.59	18U	31.50	19.00

Tags: **Pivoting Wall Rack***Data subject to change without notice*

© 2026. Hammond Manufacturing Ltd. All rights reserved.