

Low-Profile Hinged Wall-Mount Rack (50 lb) *RB-WR Series*

Compact fixed-depth wall rack with hinged access for mounting 19" equipment in shallow installations.

MOST POPULAR



RACK BASICS®

A HAMMOND BRAND



Key Features and Benefits

- 16-gauge steel construction (50 lb **capacity**) provides reliable support for lightweight network equipment and patch panels.
- Fixed 6" depth wall-mount design (19" rack compatible) supports installations where space is limited.
- Hinged design provides rear access for installation, servicing, and cable management.
- One (1) pair of 10-32 round hole mounting rails supports standard rack equipment and consistent installation. Includes mounting hardware pack with **CLPKIT10-32-10** screws, washers, and clip nuts for equipment installation.
- Available in 1U, 2U, and 4U sizes supports small-scale equipment mounting requirements.
- TAA-compliant, manufactured in North America supports government procurement requirements.
- Black powder coat finish (GREENGUARD, TSCA, RoHS compliant) supports indoor air quality and environmental compliance.

The RB-WR Series economy fixed depth wall rack provides a compact solution for mounting 19-inch rack equipment in telecom and IT environments. Constructed from 16-gauge steel with a 50 lb load capacity, the RB-WR is ideal for small network deployments, patch panels, and lightweight equipment where space and cost are key considerations.

When another product may be a better choice

- When you need a fixed wall bracket with higher capacity or deeper mounting, consider our **RB-2PW** Series.
- When you need an adjustable depth wall bracket, consider our **APB** Series.
- When you need a wall bracket with an integrated shelf, consider our **APBS** Series.

Part of the Rack Basics® line designed for simple, reliable, and affordable installations.

Accessories

- Rack Screw & Clip Nut Hardware Kit
- We Manufacture PDUs and Outlet Strips
- Ground Stud Kit



Part No.	Overall Dimensions			Rack Units	Mounting Dimensions			Weight Capacity
	Height	Width	Depth		Height	Width	Depth	
RB-WR1	1.88	19.36	6.00	1U	1.75	19.00	5.75	10 lbs (4 kg)
RB-WR2	3.62	19.36	6.00	2U	3.50	19.00	5.75	20 lbs (9 kg)
RB-WR4	7.12	19.36	6.00	4U	7.00	19.00	5.75	50 lbs (22 kg)

Where the RB-WR series works best

- Telecom backboards and network demarcation points.
- Very shallow wall-mount installations.
- Small network deployments with limited equipment.
- Retrofit installations requiring minimal wall depth.
- Installations where space and cost are primary constraints.

Applications and when to use the RB-WR series

- Installations requiring compact, shallow-depth wall mounting (6").
- Applications needing hinged access for basic servicing and cable management.
- Environments where lightweight equipment is being installed (up to 50 lb).
- Deployments requiring low-cost, space-saving mounting solutions.
- Installations where only a small number of rack units (1U–4U) are required.

Tags: **Wall mount rack 6 inch depth, shallow wall rack, hinged wall rack, compact wall rack, telecom wall rack, small wall mount rack, 1U wall rack, 2U wall rack, 4U wall rack, low profile wall rack** *Data subject to change without notice.*