



Quality Products. Service Excellence.

Adjustable Rack Mount DIN Rail Kit *RMAD Series*

TOP SELLER

Features



- Mounts to standard EIA 19" rack rails.
- Includes a 0.3" thick, top-hat standard Symmetric DIN 3 Profile DIN rail.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Finished in RAL9005 black powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS and REACH compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

RMAD (Light Duty) Features



- Constructed of 14 and 16-gauge steel.
- Provides up to 8.38" of adjustable depth for DIN rail-mounted equipment.
- Cutouts on both the rear and sides provide cable pass-through.
- 26 lbs (11 kg) load rating.

RMHD (Heavy Duty) Features

- Constructed of 14-gauge steel.
- Provides up to 8.00" of depth options for DIN rail-mounted equipment.
- 100 lbs (45 kg) load rating.

Accessories

- Hardware for Rack Mounting Solutions
- Rack Rail Reducer Panel
- Hook and Loop Convenience Roll





Part No.	Mounting Dimensions			DIN Rail Overall Dimensions		Weight Capacity
	Height	Rack Units	Depth	Width	Depth	
RMAD19003BK	3.50	2U	11.25	17.18	0.30	26 lbs
RMHD19003BK	3.50	2U	9.25	16.88	0.30	100 lbs

Tags: Industrial Automation Bracket, TransRack

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.