

Rack and Cabinet Stem Casters *RRCASTER Series*

Up to 2,000 lbs (363 kg) Weight Capacity

Features



- Features ball bearing swivel and hard composition wheels
- Stud is 1.5" (38.1 mm) long and 1/2"-13 thread
- All four (4) casters are lockable
- Includes mounting hardware
- TAA compliant for GSA Schedule purchases.
- RoHS and REACH Compliant.
- Manufactured in North America.

Compatibility

- DC4R | 4-Post Open Frame Rack
- DNRRHDKB | 2-Post Open Frame Rack
- DNRRHDW | 2-Post Open Frame Rack
- RB-2PA | 2-Post Open Frame Rack
- RB-2P | 2-Post Open Frame Rack
- HDME | NEMA 12 Equipment Cabinet
- HME | NEMA 12 Modular Enclosure
- CLC | Colocation/ Multi-Bay Server Rack Cabinet



Care should be taken in moving rack as it may be unstable depending on equipment loading pattern. Ensure weight distribution is safe for mobile use.

Part No.	Strength	Wheel Diameter	Overall Height Added to Cabinet	Caster Set Weight Capacity	Quantity Included In Set	Brakes Included
RRLDCASTER	Lite Duty	3.00	3.75	800 lbs (363 kg)	4	Yes
RRHDCASTER	Heavy Duty	3.00	3.88	2,000 lbs (907 kg)	4	Yes

Data subject to change without notice.