



NBNC75BTU11

The rearTWIST HD BNC cable connector offers a true 75 Ω design and is perfectly suitable for HD applications.

The patented rearTWIST boot guarantees easy access even in high density applications and offers color coding.

Suitable cables:

Belden 1694A (ANH), Belden 4694R, Bryant BD SD11, Canare L-4.5CHD, Clark Wire CD7506-0, CommScope 5765, Gepco VSD2001, Suhner S05163-02, Suhner S05133-07, Percon VK77

Crimp size:

Pin: 1.6 mm (square)

Shield: 7.36 mm (hex)

Features & Benefits

- ✓ “rearTWIST Principle” locking/unlocking using the easily accessible soft touch boot (Patent DE 100 48507)
- ✓ Ideal for recessed bulkheads where access to the “head” of the connector might be an issue. These connectors turn from the back and not the front.
- ✓ True 75 Ω design meets the stringent HDTV / DVD requirements
- ✓ Leading area: Avoids tilting due to side forces to protect contacts from deformation. Guarantees a lifetime of min. 1000 mating cycles!
- ✓ Snug-fit center pin insert provides tactile feedback
- ✓ Shield and jacket crimp technology prevents the problem of an exposed grounding braid on cable assemblies
- ✓ Excellent cable protection and retention

- ✓ Precise Swiss machined brass parts for outstanding durability
- ✓ Accessories include color coded boots in 10 standard colors, crimp tool and dies

Technical Information

Product	
Title	NBNC75BTU11
Connection Type	BNC 75 Ω
Gender	male

Electrical	
Contact resistance	≤ 3 mΩ (inner)
Contact resistance	≤ 2 mΩ (outer)
Dielectric strength	1,5 kVdc
Impedance	75 Ω
Insulation resistance	> 5 GΩ
Rated voltage	<50 V
VSWR	≤1.050/>32 dB up to 1 GHz ≤1.065/>30 dB up to 2 GHz ≤1.100/>26 dB up to 3 Ghz

Mechanical

Cable O.D.	7.3 mm
Cable retention	> 30 N (Center)
Crimp size	7,36 Hex crimp (shield) acc. MIL22520/5-41(A)
Crimp size (pin)	1,6 Square crimp (pin) acc. IEC 60803 (die designation 2)
Insertion force	< 25 N
Lifetime	> 1000 mating cycles
Wiresize	
Locking device	Bayonett
Cable anchoring	Jacket crimping

Material

Contacts	Brass (CuZn35Pb2), 0.2 µm AuCo (Center contact)
Insert	PTFE
Shell	Brass (CuZn39Pb3)
Shell plating	Optalloy®

Environmental

Temperature range	-30 °C to +85 °C
Contact crimpability	Complies with IEC 60803 and IEC 60352-2