

NYS352

Heavy duty phono plug, cable clamp



Article Variations

Article Name	Details	Packaging
NYS352	Nickel plated shell and contacts	
NYS352AG	Gold plated shell and contacts	
NYS352B	Black plated shell, nickel plated contacts	
NYS352BG	Black plated shell, gold plated contacts	
NYS352G	Nickel plated shell, gold plated contacts	

Technical Information

Product	
Title	NYS352
Connection Type	Plug

Electrical	
Contact resistance	$\leq 10\text{m}\Omega$
Insulation resistance	$\geq 2,000\text{M}\Omega$
Dielectric strength	50Hz 0.5KVdc

Mechanical

Insertion and Withdrawal force	5-20N
Lifetime	>5,000 mating cycles

Material

Pin	Brass
Housing	Brass
Housing	Zinc
Insulation	PP
Cable Clamp	Steel
Pin	Tin and Cer
Cable Clamp	Tin and Cer
Housing	Nickel Plating
Housing	Nickel Plating