

## RCX3M-Z

3 pole male XLR cable connector with IP65 dust-water proof design.



### Features and benefits

- ✓ IP65 rating provides outdoor protection under mated condition
- ✓ Chrome&Black plated with fashionable finish and better abrasion performance
- ✓ UL94 V-0 rated materials

### Article Variations

Article Name	Details	Packaging
RCX3M-Z-000-0/1	Chrome plated housing, tin plated contacts	BULK / Plastic Bag
RCX3M-Z-001-0/1	Black plated housing, tin plated contacts	BULK / Plastic Bag
RCX3M-Z-002-0/1	Black plated housing, gold plated contacts	BULK / Plastic Bag

## Technical Information

### Product

Title	RCX3M-Z
Connection Type	XLR
Gender	male

### Electrical

Contact resistance	$\leq 5 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	16 A
Rated voltage	$< 50 \text{ V}$

<b>Mechanical</b>	
Cable O.D.	5.0 - 8.0 mm
Insertion force	≤ 60 N
Withdrawal force	≤ 60 N
Lifetime	> 1000 cycles
Wiresize	Max. 1.5 mm <sup>2</sup>
Wiresize	Max. 16 AWG
Wiring	Solder contacts
Locking device	Latch lock

<b>Material</b>	
Bushing	Polyamide
Contact plating	Tin (-000 & - 001) / AU (-002)
Contacts	Brass
Insert	Polyamide (UL94-V0)
Locking element	Zinc diecast
Shell	Zinc diecast
Shell plating	Chrome (-000) / Black (-001 & -002)
Strain relief	Polyamide
Sealing jacket	Rubber

**Environmental**

<b>Flammability</b>	UL 94-V0
<b>Protection class</b>	IP65 (Mated)
<b>Standard compliance</b>	IEC 61076-2-103
<b>Solderability</b>	Complies with IEC 68-2-20
<b>Temperature range</b>	-20 °C to +70 °C