


4

3


2

1

REVISIONS				
ECO #	REV.	DESCRIPTION	DATE	APPROVED
9151	A	INITIAL RELEASE	09/18/24	K.KESLER



WIRING DIAGRAM



CABLE LENGTH		
PART #	SAP#	L(mm)
2664-0100	4634141002661	1000 ±20
2664-0200	4634141002662	2000 ±20
2664-0300	4634141002663	3000 ±20
2664-0500	4634141002664	5000 ±50

NOTES:

- THIS CABLE IS MANUFACTURED IN COMPLIANCE WITH THE CURRENT EU RoHS DIRECTIVE.
- ACCEPTANCE STANDARD: IPC/WHMA-A-620 CLASS 2.
- PROTECTION GRADE IP67.

CONNECTION TABLE			
PIN J1	PIN J2	SIGNAL	COLOR
1	1	TX+	BROWN
2	2	RX+	WHITE
3	3	RX-	BLUE
4	4	TX-	BLACK

 Applied Motion Products A MOONS' COMPANY PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF APPLIED MOTION PRODUCTS. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF APPLIED MOTION PRODUCTS IS PROHIBITED.	THIRD ANGLE PROJECTION		NAME	DATE	TITLE: M8 ETHERNET RIGHT ANGLED DAISY CHAIN CABLE		
	UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS	DRAWN	A. ORME	09/12/24			
	TOLERANCES: - ANGULAR: ± 0.5 - ONE DECIMAL PLACE: ± 0.25 - TWO DECIMAL PLACES: ± 0.13	PRE.CHECK	-	-			
		PRE.APPROVAL	-	-			
		FIN.CHECK	C.BREUNINGER	09/18/24			
	MATERIAL	SAP: SEE CABLE LENGTH TABLE			SIZE	DWG. NO.	REV
	FINISH	ALT DWG. NO.: -			B	2664-xxxx	A
	DO NOT SCALE DRAWING	ALT SAP: -			SCALE: 4:3		SHEET 1 OF 1

4

3

2

1