


CONNECTION TABLE		
RJ45 PIN#	DESCRIPTION	M12 PIN#
1	TWISTED PAIR	1
2		3
3	TWISTED PAIR	2
6		4
	SHIELD	METAL HOUSING


CABLE LENGTH TABLE	
FINISHED LENGTH $\pm$ 2% TOTAL	
MARK PART NO	'L'
3004-280-2M	6.5FT (2M)
3004-280-5M	16.4FT (5M)
3004-280-25M	82FT (25M)

REVISIONS				
ECO	REV	DESCRIPTION	DATE	APPROVED
6687	A	INITIAL RELEASE	2/7/13	J Kordik
6699	B	REVISED	2/20/13	J Kordik
7451	C	REVISED RoHS NOTE	6/13/16	J Kordik
7700	D	ADD -25M	8/11/17	J KORDIK



NOTES: UNLESS OTHERWISE SPECIFIED

- THIS CABLE IS MANUFACTURED IN COMPLIANCE WITH THE CURRENT EC RoHS DIRECTIVE.
- TEST 100% FOR OPENS (>1 OHMS MAX) AND SHORTS (5 MEGOHMS MIN)

TOLERANCES		THIRD ANGLE PROJECTION		 APPLIED MOTION PRODUCTS, INC.	
DECIMALS: INCH (MM) X.XXX= ±.005 X.XX = ±.010 (0.13) X.X = ±.020 (0.25) ANGLES: MACH. = ±.5° CHAM. = ±5°					
COMPUTER DATA BASE DRAWING		APPROVALS	DATE	CORD SET ETHERNET CABLE	
		DRAWN <i>R.JONEZ</i>	1/31/13		
		CHECKED		B	DWG NO. 3004-280-XXX
		APPROVED		SCALE: NTS	SHEET 1 OF 1