


CONNECTION CHART		
PIN	SIGNAL	WIRE COLOR
1	V+	BLK1
2	V-/AUX-	BLK2
3	AUX+	BLK3
4	FG/SHIELD	GRN/YEL

TABULATION CHART			
4	XXX	LENGTH	PART NUMBER
	2M	78.7" \pm 2"	3004-332-2M
	3M	118" \pm 3"	3004-332-3M
	5M	197" \pm 4"	3004-332-5M

REVISIONS				
ECO	REV	DESCRIPTION	DATE	APPROVED
7478	A	INITIAL RELEASE	8/31/16	J KORDIK
7735	B	SIGNAL CHANGE	10/17/17	J KORDIK
8743	C	CORRECTED PHOENIX PN	1/14/22	L LIU



NOTES: UNLESS OTHERWISE SPECIFIED

1. THIS CABLE IS MANUFACTURED IN COMPLIANCE WITH THE CURRENT EU RoHS DIRECTIVE.
2. WIRES WITHIN CABLE ARE BLACK, AND LABELED 1, 2, AND 3. REFER TO CONNECTION CHART FOR ASSOCIATED CONNECTOR PINS.
3. CURRENT RATING: 12A, 630VAC. RATING: IP65. TEMPERATURE RANGE: FIXED INSTALLATION -50°C TO +80°C, FLEXABLE INSTALLATION -30°C TO +80°C.
4. REFER TO TABULATION CHART FOR CABLE LENGTH.

TOLERANCES		THIRD ANGLE PROJECTION		APPLIED MOTION PRODUCTS, INC.
DECIMALS:	MM (INCH)	APPROVALS	DATE	
XXXX =	± 0.013 (.005)			
XXX =	± 0.25 (.01)			
XX =	± 2.5 (.01)			
ANGLES:				
MACH.	$\pm 5^\circ$	DRAWN	Y. LAPNET	1/14/22
CHAM.	$\pm 5^\circ$	CHECKED	K. KESLER	1/14/22
COMPUTER DATA BASE DRAWING		APPROVED		
B	DWG NO. 3004-332-XXX	REV C	SCALE: NTS	SHEET 1 OF 1