


CABLE LENGTH TABLE FINISHED LENGTH \pm 2% TOTAL	
MARK PART NO	'L'
3004-335-0.5M	0.5M (1.6 FT)
3004-335-1M	1M (3.28 FT)
3004-335-5M	5M (16.4 FT)

REVISIONS				
ECO	REV	DESCRIPTION	DATE	APPROVED
7486	A	INITIAL RELEASE	10/5/16	J KORDIK
7520	B	DOCUMENT CORRECTION	10/12/16	J Georgiana
7525	C	D-CODED, NOT S-CODED	10/18/16	J KORDIK
8518	D	TEMP -25 TO 90	7/30/20A.N.	L. LIU



NOTES: UNLESS OTHERWISE SPECIFIED

1. THIS CABLE IS MANUFACTURED IN COMPLIANCE WITH THE CURRENT EU RoHS DIRECTIVE.
2. REFER TO CONNECTION CHART FOR ASSOCIATED CONNECTOR PINS.
3. PROTECTION RATING: IP68.
TEMPERATURE RANGE: -25°C TO +90°C,
4. CABLES SUPPLIED BY L-COM: 0.5M=M12M124D-0.5,
1M=M12M124D-1, AND 5M=M12M124D-5.

TOLERANCES		THIRD ANGLE PROJECTION		APPLIED MOTION PRODUCTS, INC.	
DECIMALS: MM					
X.XXX= \pm 0.013					
X.XX = \pm 0.25					
X.X = \pm 2.5					
ANGLES:					
MACH. = \pm 5°					
CHAM. = \pm 5°					
DRAWN <i>R.JONEZ</i>		APPROVALS		DATE	
		<i>R.JONEZ</i>		8/4/16	
CHECKED <i>K.KESLER</i>		7/30/20			
APPROVED					
DWG NO.		3004-335-XXX		REV D	
SCALE: NTS		SHEET 1 OF 1			