

4

3

2





1

B

B

A

A



GEARHEAD MATERIALS:	
GEARTRAIN:	Y15 (1213) STEEL
HOUSING:	304 STAINLESS STEEL
INPUT/OUTPUT FLANGE:	LY12 ALUMINUM
OUTPUT SHAFT:	40Cr STEEL
PINION:	Y15 (1213) STEEL

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	35PH032.50-M1	PH GEARHEAD	1
2	11171924 Z/P OR EQUIVALENT	4-40 NYLON LOCKNUT	2
3	5014-042 10	STEP MOTOR	1

 Applied Motion Products A MOONS' COMPANY PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF APPLIED MOTION PRODUCTS. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF APPLIED MOTION PRODUCTS IS PROHIBITED.	UNLESS OTHERWISE SPECIFIED:		NAME	DATE	TITLE:					
	DIMENSIONS ARE IN MILLIMETERS		DRAWN	Y. LAPNET	1/28/22	STEPPER MOTOR W/ GEARHEAD				
	TOLERANCES:		CHECKED	R. BUI	1/31/22					
	ANGULAR: ± 0.5		COMMENTS:			SIZE			DWG. NO.	REV
	ONE PLACE DECIMAL ± 0.25					B	5014-042-G032	B		
TWO PLACE DECIMAL ± 0.13										
THIRD ANGLE PROJECTION		SCALE: 3:2			WEIGHT:		SHEET 2 OF 2			
MATERIAL										
FINISH										
DO NOT SCALE DRAWING										

4

3

2

1