





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
7112	5.0	.021	.034	0.43	10,000	C-2R
7114	5.0	.060	.050	0.63	100,000	C-2R
7118	5.0	.115	.150	1.89	40,000	C-2R

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE T-3/4 MICROMINIATURE BI-PIN BASED LAMPS					
B	REMOVE NOTES	1/3/22	DRAWN BY		APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.			
A	CHANGE PIN MATERIAL NOTE	7/28/08	L. WENGSTROM		SN	1/3/22	A	55335	BI-PIN T-3/4			
	RELEASED - CANCEL SM-STDBP-T 3/4, 7810,	3/15/00										
	7111, BB23, 7113, 7115, 7116, 7119											
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE		RELEASED DATE		REVISION DATE	REV. NO.	SHEET
						NONE		3/15/00		1/3/2022	B	1 OF 1